

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204046

Luminaire Tested: **LSR6B15D010BZ EC6B10208027 6LBNMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204046
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B15D010BZ EC6B10208027 6LBNMW1
Description: PORTFOLIO 6IN CYLINDER
NARROW DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1012.6 lumens
Efficiency: N/A
Efficacy: 70.8 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.99 / 0.97
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204046

CATALOG NUMBER: LSR6B15D010BZ EC6B10208027 6LBNMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204046

CATALOG NUMBER: LSR6B15D010BZ EC6B10208027 6LBNMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	108	105	103	109	106	103	101	102	100	98	98	97	95	95	93	92	90			
2	105	99	94	90	102	97	92	89	94	90	87	91	87	85	88	85	83	81			
3	98	90	84	79	96	89	83	79	86	81	77	84	80	76	81	78	75	73			
4	92	83	76	71	90	82	76	71	80	74	70	77	73	69	75	71	68	66			
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61			
6	81	71	64	59	80	70	63	59	68	63	58	67	62	58	66	61	57	56			
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51			
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47			
9	69	58	51	46	67	57	51	46	56	50	46	55	50	46	54	49	46	44			
10	65	54	47	43	64	54	47	43	53	47	43	52	46	43	51	46	43	41			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204046

CATALOG NUMBER: LSR6B15D010BZ EC6B10208027 6LBNMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.1	7.6
10°-20°	204.4	20.2
20°-30°	272.9	27.0
30°-40°	220.1	21.7
40°-50°	105.5	10.4
50°-60°	62.5	6.2
60°-70°	41.6	4.1
70°-80°	22.3	2.2
80°-90°	6.1	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	554.4	54.8
0°-40°	774.5	76.5
0°-60°	942.6	93.1
0°-90°	1012.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1012.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	830	
5°	821	77
15°	727	204
25°	597	273
35°	352	220
45°	130	106
55°	69	63
65°	42	42
75°	21	22
85°	5	6
90°	0	



TEST NUMBER: P204046

CATALOG NUMBER: LSR6B15D010BZ EC6B10208027 6LBNMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	830.4
2.5°	830.4
5°	820.8
7.5°	804.7
10°	782.1
12.5°	758.0
15°	727.4
17.5°	698.4
20°	666.3
22.5°	632.5
25°	597.1
27.5°	560.0
30°	506.9
32.5°	432.9
35°	352.4
37.5°	278.4
40°	215.7
42.5°	167.4
45°	130.4
47.5°	103.0
50°	86.9
52.5°	77.2
55°	69.2
57.5°	62.8
60°	54.7
62.5°	48.3
65°	41.8
67.5°	35.4
70°	30.6
72.5°	25.7
75°	20.9
77.5°	16.1
80°	12.9
82.5°	9.7
85°	4.8
87.5°	1.6
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)