

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204666

Luminaire Tested: **LSR6B15D010BZ EC6B10208027 6LBPSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204666
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B15D010BZ EC6B10208027 6LBPSMW1
Description: PORTFOLIO 6IN CYLINDER
SHALLOW DISTRIBUTION WITH PLASTIC MATTE WHITE TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1574.4 lumens
Efficiency: N/A
Efficacy: 110.1 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204666

CATALOG NUMBER: LSR6B15D010BZ EC6B10208027 6LBPSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204666

CATALOG NUMBER: LSR6B15D010BZ EC6B10208027 6LBPSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86																			
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74																			
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63																			
4	85	74	65	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54																			
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47																			
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42																			
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37																			
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33																			
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30																			
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204666

CATALOG NUMBER: LSR6B15D010BZ EC6B10208027 6LBPSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	60.1	3.8
10°-20°	171.3	10.9
20°-30°	258.0	16.4
30°-40°	307.0	19.5
40°-50°	306.5	19.5
50°-60°	249.2	15.8
60°-70°	153.3	9.7
70°-80°	59.4	3.8
80°-90°	9.5	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	489.5	31.1
0°-40°	796.5	50.6
0°-60°	1352.2	85.9
0°-90°	1574.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1574.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	634	
5°	632	60
15°	608	171
25°	562	258
35°	492	307
45°	398	306
55°	279	249
65°	154	153
75°	54	59
85°	8	10
90°	0	



TEST NUMBER: P204666

CATALOG NUMBER: LSR6B15D010BZ EC6B10208027 6LBPSMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	634.3
2.5°	635.3
5°	632.5
7.5°	628.7
10°	624.1
12.5°	615.7
15°	608.2
17.5°	597.0
20°	584.9
22.5°	573.7
25°	561.6
27.5°	544.8
30°	528.0
32.5°	512.1
35°	491.6
37.5°	469.2
40°	448.7
42.5°	423.5
45°	398.3
47.5°	371.3
50°	342.4
52.5°	312.5
55°	278.9
57.5°	246.3
60°	214.6
62.5°	183.8
65°	153.9
67.5°	125.9
70°	99.8
72.5°	75.6
75°	54.1
77.5°	35.4
80°	21.5
82.5°	13.1
85°	7.5
87.5°	3.7
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)