

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204775

Luminaire Tested: **LSR6B15D010BZ EC6B10209027 6LBCSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204775
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B15D010BZ EC6B10209027 6LBCSMW1
Description: PORTFOLIO 6IN CYLINDER
SHALLOW DISTRIBUTION WITH CAST MATTE WHITE TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1323.0 lumens
Efficiency: N/A
Efficacy: 92.5 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204775

CATALOG NUMBER: LSR6B15D010BZ EC6B10209027 6LBCSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204775

CATALOG NUMBER: LSR6B15D010BZ EC6B10209027 6LBCSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87			
2	101	94	87	82	99	92	86	81	88	84	79	85	81	78	82	79	76	74			
3	93	83	75	70	90	81	74	69	79	73	68	76	71	67	73	69	65	63			
4	85	74	66	60	83	73	65	59	70	64	58	68	62	58	66	61	57	55			
5	79	66	58	52	77	65	57	51	63	56	51	61	55	50	60	54	50	48			
6	73	60	52	45	71	59	51	45	57	50	45	56	49	44	54	49	44	42			
7	68	55	46	40	66	54	46	40	52	45	40	51	44	40	50	44	39	37			
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	33			
9	59	46	38	33	57	45	38	32	44	37	32	43	37	32	42	36	32	30			
10	55	42	35	30	54	42	34	30	41	34	29	40	34	29	39	33	29	27			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204775

CATALOG NUMBER: LSR6B15D010BZ EC6B10209027 6LBCSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.2	3.9
10°-20°	145.8	11.0
20°-30°	219.3	16.6
30°-40°	259.8	19.6
40°-50°	258.6	19.5
50°-60°	208.5	15.8
60°-70°	126.1	9.5
70°-80°	46.8	3.5
80°-90°	7.0	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	416.2	31.5
0°-40°	676.0	51.1
0°-60°	1143.1	86.4
0°-90°	1323.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1323.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	540	
5°	538	51
15°	516	146
25°	476	219
35°	416	260
45°	337	259
55°	232	208
65°	127	126
75°	42	47
85°	6	7
90°	0	



TEST NUMBER: P204775

CATALOG NUMBER: LSR6B15D010BZ EC6B10209027 6LBCSMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	540.3
2.5°	540.3
5°	537.9
7.5°	536.3
10°	531.5
12.5°	523.5
15°	516.3
17.5°	508.3
20°	498.7
22.5°	489.0
25°	476.2
27.5°	462.6
30°	447.3
32.5°	432.9
35°	416.1
37.5°	398.4
40°	377.6
42.5°	357.6
45°	336.7
47.5°	313.5
50°	287.8
52.5°	261.4
55°	232.5
57.5°	206.8
60°	178.0
62.5°	152.3
65°	126.7
67.5°	102.6
70°	80.2
72.5°	60.1
75°	42.5
77.5°	27.3
80°	16.0
82.5°	9.6
85°	5.6
87.5°	2.4
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)