

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203233

Luminaire Tested: **LSR6B15D010BZ EC6B10209727 6LBMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203233
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B15D010BZ EC6B10209727 6LBMH1
Description: PORTFOLIO 6IN CYLINDER
MEDIUM DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 765.3 lumens
Efficiency: N/A
Efficacy: 53.5 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.93
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203233

CATALOG NUMBER: LSR6B15D010BZ EC6B10209727 6LBMH1

Luminous Intensity Polar Plot





TEST NUMBER: P203233

CATALOG NUMBER: LSR6B15D010BZ EC6B10209727 6LBMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	92		
2	107	102	97	93	105	100	96	92	97	93	90	94	91	88	91	89	87	85		
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78		
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72		
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66		
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61		
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57		
8	76	66	60	55	75	65	59	55	64	59	55	63	58	55	62	58	54	53		
9	72	62	56	51	71	61	55	51	60	55	51	60	55	51	59	54	51	49		
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	55	51	48	46		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203233

CATALOG NUMBER: LSR6B15D010BZ EC6B10209727 6LBMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	69.2	9.0
10°-20°	179.1	23.4
20°-30°	232.1	30.3
30°-40°	172.3	22.5
40°-50°	72.7	9.5
50°-60°	25.8	3.4
60°-70°	9.9	1.3
70°-80°	3.5	0.5
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	480.5	62.8
0°-40°	652.8	85.3
0°-60°	751.4	98.2
0°-90°	765.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	765.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	757	
5°	741	69
15°	639	179
25°	515	232
35°	273	172
45°	90	73
55°	27	26
65°	10	10
75°	3	3
85°	0	0
90°	0	



TEST NUMBER: P203233

CATALOG NUMBER: LSR6B15D010BZ EC6B10209727 6LBMH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	757.3
2.5°	755.1
5°	740.9
7.5°	720.2
10°	695.0
12.5°	667.7
15°	639.3
17.5°	607.6
20°	579.2
22.5°	549.7
25°	514.7
27.5°	466.6
30°	409.8
32.5°	343.1
35°	273.2
37.5°	214.2
40°	162.8
42.5°	121.3
45°	89.6
47.5°	65.6
50°	48.1
52.5°	36.1
55°	27.3
57.5°	20.8
60°	16.4
62.5°	12.0
65°	9.8
67.5°	7.6
70°	5.5
72.5°	4.4
75°	3.3
77.5°	2.2
80°	1.1
82.5°	1.1
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)