

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203542

Luminaire Tested: **LSR6B15D010BZ EC6B10209727 6LBMMW1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P203542  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR6B15D010BZ EC6B10209727 6LBMMW1  
Description: PORTFOLIO 6IN CYLINDER  
MEDIUM DISTRIBUTION WITH MATTE WHITE TRIM  
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W  
DL3-15.28 W DLE-15.432 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 839.6 lumens  
Efficiency: N/A  
Efficacy: 58.7 lumens/watt  
Spacing Criteria (0/90/45): 1 / 1 / 0.97  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 14.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P203542

CATALOG NUMBER: LSR6B15D010BZ EC6B10209727 6LBMMW1

### Luminous Intensity Polar Plot





TEST NUMBER: P203542

CATALOG NUMBER: LSR6B15D010BZ EC6B10209727 6LBMMW1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	108	104	101	109	105	103	100	101	99	97	98	96	94	94	92	91	89		
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79		
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71		
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	65	64		
5	85	74	67	61	83	73	66	61	71	65	61	69	64	60	68	63	59	58		
6	79	68	61	56	78	68	61	56	66	60	55	64	59	55	63	58	54	53		
7	75	63	56	51	73	63	56	51	61	55	50	60	54	50	59	54	50	48		
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44		
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	43	41		
10	63	51	45	40	62	51	44	40	50	44	40	49	44	40	48	43	40	38		

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P203542

CATALOG NUMBER: LSR6B15D010BZ EC6B10209727 6LBMMW1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	57.9	6.9
10°-20°	155.0	18.5
20°-30°	208.1	24.8
30°-40°	170.7	20.3
40°-50°	102.5	12.2
50°-60°	68.1	8.1
60°-70°	45.7	5.4
70°-80°	24.6	2.9
80°-90°	6.9	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	421.0	50.1
0°-40°	591.8	70.5
0°-60°	762.4	90.8
0°-90°	839.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	839.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	626	
5°	616	58
15°	552	155
25°	459	208
35°	271	171
45°	130	103
55°	75	68
65°	46	46
75°	23	25
85°	6	7
90°	0	



TEST NUMBER: P203542

CATALOG NUMBER: LSR6B15D010BZ EC6B10209727 6LBMMW1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	626.5
2.5°	621.9
5°	616.1
7.5°	603.3
10°	588.3
12.5°	569.8
15°	552.4
17.5°	531.5
20°	510.7
22.5°	487.5
25°	458.6
27.5°	423.8
30°	377.5
32.5°	325.4
35°	271.0
37.5°	224.7
40°	185.3
42.5°	154.0
45°	129.7
47.5°	110.0
50°	96.1
52.5°	84.5
55°	75.3
57.5°	67.2
60°	60.2
62.5°	52.1
65°	46.3
67.5°	39.4
70°	33.6
72.5°	27.8
75°	23.2
77.5°	18.5
80°	13.9
82.5°	10.4
85°	5.8
87.5°	2.3
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)