

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P202924

Luminaire Tested: **LSR6B15D010BZ EC6B10209727 6LBWGPH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P202924  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR6B15D010BZ EC6B10209727 6LBWGPH1  
Description: PORTFOLIO 6IN CYLINDER  
WIDE DISTRIBUTIONWITH GRAPHITE HAZE TRIM  
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W  
DL3-15.28 W DLE-15.432 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 696.9 lumens  
Efficiency: N/A  
Efficacy: 48.7 lumens/watt  
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.11  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 14.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P202924

CATALOG NUMBER: LSR6B15D010BZ EC6B10209727 6LBWGPH1

### Luminous Intensity Polar Plot





TEST NUMBER: P202924

CATALOG NUMBER: LSR6B15D010BZ EC6B10209727 6LBWGPH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	82																			
3	99	91	85	81	97	90	84	80	87	82	79	85	81	77	82	79	76	74																			
4	93	84	77	72	91	82	76	72	80	75	71	78	74	70	76	72	69	67																			
5	87	77	70	65	85	76	69	65	74	68	64	72	67	63	71	66	63	61																			
6	81	71	64	59	80	70	63	58	68	62	58	67	62	58	65	61	57	56																			
7	76	65	58	53	75	65	58	53	63	57	53	62	57	53	61	56	52	51																			
8	72	61	54	49	70	60	53	49	59	53	49	58	52	48	57	52	48	47																			
9	68	57	50	45	66	56	49	45	55	49	45	54	48	45	53	48	44	43																			
10	64	53	46	42	63	52	46	42	51	45	41	51	45	41	50	45	41	40																			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P202924

CATALOG NUMBER: LSR6B15D010BZ EC6B10209727 6LBWGPH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	44.6	6.4
10°-20°	125.1	18.0
20°-30°	179.0	25.7
30°-40°	178.4	25.6
40°-50°	113.6	16.3
50°-60°	41.9	6.0
60°-70°	10.5	1.5
70°-80°	3.2	0.5
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	348.8	50.0
0°-40°	527.2	75.6
0°-60°	682.8	98.0
0°-90°	696.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	696.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	474	
5°	471	45
15°	445	125
25°	391	179
35°	290	178
45°	146	114
55°	44	42
65°	10	10
75°	2	3
85°	0	0
90°	0	



TEST NUMBER: P202924

CATALOG NUMBER: LSR6B15D010BZ EC6B10209727 6LBWGPH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	473.7
2.5°	473.7
5°	471.3
7.5°	466.5
10°	460.5
12.5°	453.3
15°	444.9
17.5°	434.1
20°	422.1
22.5°	408.9
25°	390.9
27.5°	371.7
30°	346.5
32.5°	320.2
35°	290.2
37.5°	254.2
40°	217.0
42.5°	181.1
45°	146.3
47.5°	115.1
50°	86.3
52.5°	63.6
55°	44.4
57.5°	28.8
60°	19.2
62.5°	13.2
65°	9.6
67.5°	7.2
70°	6.0
72.5°	3.6
75°	2.4
77.5°	2.4
80°	1.2
82.5°	1.2
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)