

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P202718

Luminaire Tested: **LSR6B15D010BZ EC6B10209727 6LBWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P202718
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B15D010BZ EC6B10209727 6LBWH1
Description: PORTFOLIO 6IN CYLINDER
WIDE DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 926.1 lumens
Efficiency: N/A
Efficacy: 64.8 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.16
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P202718

CATALOG NUMBER: LSR6B15D010BZ EC6B10209727 6LBWH1

Luminous Intensity Polar Plot





TEST NUMBER: P202718

CATALOG NUMBER: LSR6B15D010BZ EC6B10209727 6LBWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																					
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	112	109	106	103	110	107	104	101	103	100	98	99	97	95	95	94	93	91																																				
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81																																				
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	78	75	73																																				
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65																																				
5	86	75	68	63	84	74	68	63	72	66	62	71	65	61	69	64	61	59																																				
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53																																				
7	75	64	56	51	73	63	56	51	62	55	51	60	55	51	59	54	50	49																																				
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44																																				
9	66	55	48	43	65	54	47	43	53	47	43	52	47	42	51	46	42	41																																				
10	62	51	44	40	61	50	44	39	50	43	39	49	43	39	48	43	39	38																																				

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P202718

CATALOG NUMBER: LSR6B15D010BZ EC6B10209727 6LBWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.9	5.8
10°-20°	153.1	16.5
20°-30°	224.4	24.2
30°-40°	233.6	25.2
40°-50°	161.6	17.5
50°-60°	70.4	7.6
60°-70°	21.6	2.3
70°-80°	6.5	0.7
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	431.5	46.6
0°-40°	665.1	71.8
0°-60°	897.1	96.9
0°-90°	926.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	926.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	571	
5°	569	54
15°	544	153
25°	491	224
35°	378	234
45°	209	162
55°	76	70
65°	20	22
75°	6	6
85°	1	1
90°	0	



TEST NUMBER: P202718

CATALOG NUMBER: LSR6B15D010BZ EC6B10209727 6LBWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	571.2
2.5°	572.4
5°	568.8
7.5°	564.0
10°	558.0
12.5°	552.0
15°	543.6
17.5°	532.8
20°	520.8
22.5°	507.6
25°	490.8
27.5°	469.2
30°	441.6
32.5°	412.8
35°	378.0
37.5°	339.6
40°	295.2
42.5°	250.8
45°	208.8
47.5°	169.2
50°	134.4
52.5°	102.0
55°	75.6
57.5°	54.0
60°	37.2
62.5°	27.6
65°	20.4
67.5°	15.6
70°	10.8
72.5°	8.4
75°	6.0
77.5°	3.6
80°	2.4
82.5°	1.2
85°	1.2
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)