

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203532

Luminaire Tested: **LSR6B15D010BZ EC6B10208030 6LBMMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203532
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B15D010BZ EC6B10208030 6LBMMW1
Description: PORTFOLIO 6IN CYLINDER
MEDIUM DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1175.7 lumens
Efficiency: N/A
Efficacy: 82.2 lumens/watt
Spacing Criteria (0/90/45): 1 / 1 / 0.97
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203532

CATALOG NUMBER: LSR6B15D010BZ EC6B10208030 6LBMMW1

Luminous Intensity Polar Plot





TEST NUMBER: P203532

CATALOG NUMBER: LSR6B15D010BZ EC6B10208030 6LBMMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	111	108	104	101	109	105	103	100	101	99	97	98	96	94	94	92	91	89		
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79		
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71		
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	65	64		
5	85	74	67	61	83	73	66	61	71	65	61	69	64	60	68	63	59	58		
6	79	68	61	56	78	68	61	56	66	60	55	64	59	55	63	58	54	53		
7	75	63	56	51	73	63	56	51	61	55	50	60	54	50	59	54	50	48		
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44		
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	43	41		
10	63	51	45	40	62	51	44	40	50	44	40	49	44	40	48	43	40	38		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203532

CATALOG NUMBER: LSR6B15D010BZ EC6B10208030 6LBMMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.0	6.9
10°-20°	217.1	18.5
20°-30°	291.5	24.8
30°-40°	239.1	20.3
40°-50°	143.6	12.2
50°-60°	95.4	8.1
60°-70°	64.0	5.4
70°-80°	34.4	2.9
80°-90°	9.7	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	589.6	50.1
0°-40°	828.7	70.5
0°-60°	1067.7	90.8
0°-90°	1175.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1175.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	877	
5°	863	81
15°	774	217
25°	642	291
35°	380	239
45°	182	144
55°	105	95
65°	65	64
75°	32	34
85°	8	10
90°	0	



TEST NUMBER: P203532

CATALOG NUMBER: LSR6B15D010BZ EC6B10208030 6LBMMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	877.3
2.5°	870.8
5°	862.7
7.5°	844.9
10°	823.8
12.5°	797.8
15°	773.5
17.5°	744.3
20°	715.1
22.5°	682.7
25°	642.2
27.5°	593.5
30°	528.6
32.5°	455.7
35°	379.5
37.5°	314.6
40°	259.5
42.5°	215.7
45°	181.6
47.5°	154.1
50°	134.6
52.5°	118.4
55°	105.4
57.5°	94.1
60°	84.3
62.5°	73.0
65°	64.9
67.5°	55.1
70°	47.0
72.5°	38.9
75°	32.4
77.5°	25.9
80°	19.5
82.5°	14.6
85°	8.1
87.5°	3.2
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)