

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205280

Luminaire Tested: **LSR6B15D010BZ EC6B10208030 6LBNI1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P205280  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR6B15D010BZ EC6B10208030 6LBNLI1  
Description: PORTFOLIO 6IN CYLINDER  
NARROW DISTRIBUTION WITH SPECULAR CLEAR TRIM  
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W  
DL3-15.28 W DLE-15.432 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1165.7 lumens  
Efficiency: N/A  
Efficacy: 81.5 lumens/watt  
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.58  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 14.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P205280

CATALOG NUMBER: LSR6B15D010BZ EC6B10208030 6LBNLI1

### Luminous Intensity Polar Plot





TEST NUMBER: P205280

CATALOG NUMBER: LSR6B15D010BZ EC6B10208030 6LBNLI1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	112	109	107	112	109	107	106	105	104	102	102	101	99	98	97	96	95			
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	89			
3	105	99	94	91	103	97	93	90	95	91	89	93	90	87	90	88	86	85			
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	80			
5	96	88	83	79	94	87	83	79	86	82	78	84	81	78	83	80	77	76			
6	92	84	79	75	90	83	78	75	82	77	74	80	76	74	79	76	73	72			
7	88	80	74	71	87	79	74	71	78	73	70	77	73	70	76	72	69	68			
8	84	76	71	67	83	75	70	67	74	70	67	73	69	66	73	69	66	65			
9	81	73	67	64	80	72	67	64	71	67	63	70	66	63	70	66	63	62			
10	78	69	64	61	77	69	64	61	68	64	61	67	63	60	67	63	60	59			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P205280

CATALOG NUMBER: LSR6B15D010BZ EC6B10208030 6LBNLI1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	220.7	18.9
10°-20°	396.1	34.0
20°-30°	320.2	27.5
30°-40°	184.5	15.8
40°-50°	39.0	3.3
50°-60°	3.4	0.3
60°-70°	1.7	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	936.9	80.4
0°-40°	1121.4	96.2
0°-60°	1163.8	99.8
0°-90°	1165.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1165.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2654	
5°	2472	221
15°	1439	396
25°	691	320
35°	292	184
45°	42	39
55°	3	3
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P205280

CATALOG NUMBER: LSR6B15D010BZ EC6B10208030 6LBNLI1

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2654.0
2.5°	2622.1
5°	2472.5
7.5°	2257.3
10°	1993.4
12.5°	1722.8
15°	1438.8
17.5°	1164.8
20°	964.8
22.5°	811.8
25°	690.8
27.5°	588.3
30°	495.8
32.5°	393.3
35°	292.5
37.5°	203.4
40°	132.8
42.5°	80.7
45°	42.0
47.5°	16.8
50°	5.0
52.5°	5.0
55°	3.4
57.5°	3.4
60°	1.7
62.5°	1.7
65°	1.7
67.5°	1.7
70°	1.7
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)