

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204459

Luminaire Tested: **LSR6B15D010BZ EC6B10208030 6LBSB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204459
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B15D010BZ EC6B10208030 6LBSB1
Description: PORTFOLIO 6IN CYLINDER
SHALLOW DISTRIBUTION WITH SPECULAR BLACK TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1342.0 lumens
Efficiency: N/A
Efficacy: 93.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.3
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204459

CATALOG NUMBER: LSR6B15D010BZ EC6B10208030 6LBSB1

Luminous Intensity Polar Plot





TEST NUMBER: P204459

CATALOG NUMBER: LSR6B15D010BZ EC6B10208030 6LBSB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	103	100	108	105	101	98	100	98	95	97	94	93	93	91	90	88																			
2	102	95	89	84	100	93	88	83	90	85	81	86	83	79	84	80	78	76																			
3	94	84	77	72	91	83	76	71	80	74	70	77	73	68	75	71	67	65																			
4	86	76	68	62	84	74	67	61	72	65	60	70	64	60	68	63	59	57																			
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50																			
6	74	62	53	47	72	61	53	47	59	52	47	57	51	46	56	50	46	44																			
7	69	56	48	42	67	55	48	42	54	47	42	52	46	41	51	45	41	39																			
8	64	51	43	38	63	51	43	38	49	42	37	48	42	37	47	41	37	35																			
9	60	47	39	34	59	47	39	34	46	39	34	45	38	34	44	38	34	32																			
10	56	44	36	31	55	43	36	31	42	36	31	41	35	31	40	35	31	29																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204459

CATALOG NUMBER: LSR6B15D010BZ EC6B10208030 6LBSB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.9	4.2
10°-20°	158.5	11.8
20°-30°	235.8	17.6
30°-40°	274.4	20.4
40°-50°	267.5	19.9
50°-60°	205.7	15.3
60°-70°	113.7	8.5
70°-80°	30.1	2.2
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	450.3	33.6
0°-40°	724.7	54.0
0°-60°	1197.9	89.3
0°-90°	1342.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1342.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	592	
5°	589	56
15°	561	159
25°	512	236
35°	441	274
45°	347	267
55°	230	206
65°	114	114
75°	26	30
85°	0	0
90°	0	



TEST NUMBER: P204459

CATALOG NUMBER: LSR6B15D010BZ EC6B10208030 6LBSB1

CANDELA DISTRIBUTION (FULL):

	0°
0°	592.0
2.5°	592.0
5°	588.6
7.5°	583.5
10°	580.1
12.5°	569.9
15°	561.4
17.5°	552.9
20°	541.0
22.5°	529.1
25°	512.1
27.5°	495.0
30°	478.0
32.5°	459.3
35°	440.6
37.5°	416.8
40°	396.4
42.5°	374.3
45°	347.0
47.5°	321.5
50°	292.6
52.5°	262.0
55°	229.7
57.5°	199.0
60°	170.1
62.5°	141.2
65°	114.0
67.5°	88.5
70°	64.6
72.5°	44.2
75°	25.5
77.5°	11.9
80°	1.7
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)