

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P795071

Luminaire Tested: LER6D65D010-EC6DR7055659024-6LBDP1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P795071
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D65D010-EC6DR7055659024-6LBDDP1B
Description: 6 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3985.1 lumens
Efficiency: N/A
Efficacy: 54.7 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 72.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P795071
CATALOG NUMBER: LER6D65D010-EC6DR7055659024-6LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P795071

CATALOG NUMBER: LER6D65D010-EC6DR7055659024-6LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	489532
5°	474983
10°	461747
15°	455684
20°	425512
25°	319666
30°	225984
35°	80043
40°	42090
45°	44826
50°	46421
55°	47299
60°	47594
65°	46588
70°	43957
75°	40738
80°	36179
85°	29335

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 47605 cd/sqm



TEST NUMBER: P795071

CATALOG NUMBER: LER6D65D010-EC6DR7055659024-6LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	408.5	10.3
10°-20°	1120.4	28.1
20°-30°	1234.0	31.0
30°-40°	471.5	11.8
40°-50°	222.6	5.6
50°-60°	221.3	5.6
60°-70°	177.2	4.4
70°-80°	101.8	2.6
80°-90°	27.7	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2762.9	69.3
0°-40°	3234.4	81.2
0°-60°	3678.3	92.3
0°-90°	3985.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3985.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4480	
5°	4331	408
15°	4028	1120
25°	2652	1234
35°	600	471
45°	290	223
55°	248	221
65°	180	177
75°	96	102
85°	23	28
90°	0	



TEST NUMBER: P795071

CATALOG NUMBER: LER6D65D010-EC6DR7055659024-6LBDP1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	4480.4
2.5°	4433.6
5°	4330.7
7.5°	4244.9
10°	4161.9
12.5°	4091.6
15°	4028.5
17.5°	3876.0
20°	3659.6
22.5°	3192.9
25°	2651.6
27.5°	2308.3
30°	1791.2
32.5°	1157.0
35°	600.1
37.5°	324.2
40°	295.1
42.5°	293.0
45°	290.1
47.5°	283.7
50°	273.1
52.5°	261.0
55°	248.3
57.5°	234.1
60°	217.8
62.5°	199.3
65°	180.2
67.5°	158.9
70°	137.6
72.5°	116.3
75°	96.5
77.5°	75.9
80°	57.5
82.5°	40.4
85°	23.4
87.5°	9.2
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)