

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P795074

Luminaire Tested: LER6D65D010-EC6DR7055659024-6LBDP1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P795074
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D65D010-EC6DR7055659024-6LB DP1MW
Description: 6 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5350.0 lumens
Efficiency: N/A
Efficacy: 73.5 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 72.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P795074
CATALOG NUMBER: LER6D65D010-EC6DR7055659024-6LB DP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P795074

CATALOG NUMBER: LER6D65D010-EC6DR7055659024-6LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	657193
5°	637658
10°	619890
15°	611760
20°	571249
25°	429155
30°	303373
35°	107466
40°	56510
45°	60185
50°	62315
55°	63490
60°	63896
65°	62539
70°	59036
75°	54669
80°	48512
85°	39364

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 63913 cd/sqm



TEST NUMBER: P795074

CATALOG NUMBER: LER6D65D010-EC6DR7055659024-6LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	548.4	10.3
10°-20°	1504.2	28.1
20°-30°	1656.7	31.0
30°-40°	633.0	11.8
40°-50°	298.9	5.6
50°-60°	297.1	5.6
60°-70°	237.9	4.4
70°-80°	136.7	2.6
80°-90°	37.2	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3709.2	69.3
0°-40°	4342.2	81.2
0°-60°	4938.2	92.3
0°-90°	5350.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5350.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6015	
5°	5814	548
15°	5408	1504
25°	3560	1657
35°	806	633
45°	390	299
55°	333	297
65°	242	238
75°	130	137
85°	31	37
90°	0	



TEST NUMBER: P795074

CATALOG NUMBER: LER6D65D010-EC6DR7055659024-6LBDP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	6014.9
2.5°	5952.0
5°	5813.9
7.5°	5698.7
10°	5587.3
12.5°	5493.0
15°	5408.3
17.5°	5203.5
20°	4913.0
22.5°	4286.4
25°	3559.8
27.5°	3098.9
30°	2404.6
32.5°	1553.2
35°	805.7
37.5°	435.2
40°	396.2
42.5°	393.3
45°	389.5
47.5°	380.9
50°	366.6
52.5°	350.5
55°	333.3
57.5°	314.3
60°	292.4
62.5°	267.6
65°	241.9
67.5°	213.3
70°	184.8
72.5°	156.2
75°	129.5
77.5°	101.9
80°	77.1
82.5°	54.3
85°	31.4
87.5°	12.4
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)