

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203847

Luminaire Tested: **LSR6B15D010BZ EC6B10209030 6LBNGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203847
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B15D010BZ EC6B10209030 6LBNGPH1
Description: PORTFOLIO 6IN CYLINDER
NARROW DISTRIBUTION WITH GRAPHITE HAZE TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 629.9 lumens
Efficiency: N/A
Efficacy: 44.1 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.88
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203847

CATALOG NUMBER: LSR6B15D010BZ EC6B10209030 6LBNGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P203847

CATALOG NUMBER: LSR6B15D010BZ EC6B10209030 6LBNGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									20
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	97	96	95	94																												
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	91	89	87																												
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81																												
4	97	90	84	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76																												
5	93	84	78	74	91	83	78	74	82	77	73	80	76	73	78	75	72	70																												
6	88	79	73	69	86	78	73	69	77	72	68	75	71	68	74	70	67	66																												
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62																												
8	80	70	64	60	78	69	64	60	68	63	60	67	63	59	66	62	59	58																												
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56	54																												
10	72	63	57	53	71	62	57	53	61	56	53	61	56	53	60	56	52	51																												

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203847

CATALOG NUMBER: LSR6B15D010BZ EC6B10209030 6LBNGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	69.3	11.0
10°-20°	171.0	27.1
20°-30°	207.1	32.9
30°-40°	141.2	22.4
40°-50°	33.6	5.3
50°-60°	5.3	0.8
60°-70°	1.9	0.3
70°-80°	0.5	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	447.4	71.0
0°-40°	588.6	93.4
0°-60°	627.5	99.6
0°-90°	629.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	629.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	766	
5°	744	69
15°	612	171
25°	452	207
35°	226	141
45°	36	34
55°	6	5
65°	1	2
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P203847

CATALOG NUMBER: LSR6B15D010BZ EC6B10209030 6LBNGPH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	765.7
2.5°	761.4
5°	744.2
7.5°	721.2
10°	688.1
12.5°	650.8
15°	612.0
17.5°	571.8
20°	531.6
22.5°	491.3
25°	452.5
27.5°	416.6
30°	364.9
32.5°	297.4
35°	225.6
37.5°	160.9
40°	106.3
42.5°	66.1
45°	35.9
47.5°	18.7
50°	10.1
52.5°	7.2
55°	5.7
57.5°	4.3
60°	2.9
62.5°	2.9
65°	1.4
67.5°	1.4
70°	1.4
72.5°	1.4
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)