

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P795096

Luminaire Tested: LER6D65D010-EC6DR7055659035-6LBDP1H

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P795096  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LER6D65D010-EC6DR7055659035-6LBDP1H  
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 70° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8077.4 lumens  
Efficiency: N/A  
Efficacy: 111.0 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct


Input Watts (W): 72.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



Downlight

TEST NUMBER: P795096  
CATALOG NUMBER: LER6D65D010-EC6DR7055659035-6LBDP1H

### Luminous Intensity Polar Plot





TEST NUMBER: P795096

CATALOG NUMBER: LER6D65D010-EC6DR7055659035-6LBDP1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	992241
5°	962754
10°	935921
15°	923641
20°	862489
25°	647940
30°	458036
35°	162247
40°	85307
45°	90872
50°	94101
55°	95855
60°	96455
65°	94416
70°	89097
75°	82531
80°	73303
85°	59422

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 57.5°  
 Luminance: 96490 cd/sqm



TEST NUMBER: P795096

CATALOG NUMBER: LER6D65D010-EC6DR7055659035-6LBDP1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	828.0	10.3
10°-20°	2271.0	28.1
20°-30°	2501.2	31.0
30°-40°	955.6	11.8
40°-50°	451.2	5.6
50°-60°	448.6	5.6
60°-70°	359.2	4.4
70°-80°	206.4	2.6
80°-90°	56.1	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5600.2	69.3
0°-40°	6555.9	81.2
0°-60°	7455.7	92.3
0°-90°	8077.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8077.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	9081	
5°	8778	828
15°	8166	2271
25°	5375	2501
35°	1216	956
45°	588	451
55°	503	449
65°	365	359
75°	196	206
85°	47	56
90°	0	



TEST NUMBER: P795096

CATALOG NUMBER: LER6D65D010-EC6DR7055659035-6LBDP1H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	9081.4
2.5°	8986.5
5°	8778.0
7.5°	8604.0
10°	8435.8
12.5°	8293.4
15°	8165.5
17.5°	7856.3
20°	7417.8
22.5°	6471.7
25°	5374.6
27.5°	4678.7
30°	3630.5
32.5°	2345.1
35°	1216.4
37.5°	657.1
40°	598.1
42.5°	593.8
45°	588.1
47.5°	575.1
50°	553.6
52.5°	529.1
55°	503.2
57.5°	474.5
60°	441.4
62.5°	404.0
65°	365.2
67.5°	322.1
70°	278.9
72.5°	235.8
75°	195.5
77.5°	153.8
80°	116.5
82.5°	82.0
85°	47.4
87.5°	18.7
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)