

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204673

Luminaire Tested: **LSR6B15D010BZ EC6B10209030 6LBPSMW1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P204673  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR6B15D010BZ EC6B10209030 6LBPSMW1  
Description: PORTFOLIO 6IN CYLINDER  
SHALLOW DISTRIBUTION WITH PLASTIC MATTE WHITE TRIM  
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W  
DL3-15.28 W DLE-15.432 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1405.7 lumens  
Efficiency: N/A  
Efficacy: 98.3 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 14.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P204673

CATALOG NUMBER: LSR6B15D010BZ EC6B10209030 6LBPSMW1

### Luminous Intensity Polar Plot





TEST NUMBER: P204673

CATALOG NUMBER: LSR6B15D010BZ EC6B10209030 6LBPSMW1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86				86
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74				74
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63				63
4	85	74	65	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54				54
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47				47
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42				42
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37				37
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33				33
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30				30
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27				27

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P204673

CATALOG NUMBER: LSR6B15D010BZ EC6B10209030 6LBPSMW1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	53.7	3.8
10°-20°	153.0	10.9
20°-30°	230.4	16.4
30°-40°	274.1	19.5
40°-50°	273.6	19.5
50°-60°	222.5	15.8
60°-70°	136.9	9.7
70°-80°	53.0	3.8
80°-90°	8.5	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	437.0	31.1
0°-40°	711.1	50.6
0°-60°	1207.2	85.9
0°-90°	1405.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1405.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	566	
5°	565	54
15°	543	153
25°	501	230
35°	439	274
45°	356	274
55°	249	223
65°	137	137
75°	48	53
85°	7	9
90°	0	



TEST NUMBER: P204673

CATALOG NUMBER: LSR6B15D010BZ EC6B10209030 6LBPSMW1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	566.4
2.5°	567.2
5°	564.7
7.5°	561.4
10°	557.2
12.5°	549.7
15°	543.0
17.5°	533.0
20°	522.2
22.5°	512.2
25°	501.4
27.5°	486.4
30°	471.4
32.5°	457.2
35°	438.9
37.5°	418.9
40°	400.6
42.5°	378.1
45°	355.6
47.5°	331.5
50°	305.7
52.5°	279.0
55°	249.0
57.5°	219.9
60°	191.6
62.5°	164.1
65°	137.4
67.5°	112.4
70°	89.1
72.5°	67.5
75°	48.3
77.5°	31.6
80°	19.2
82.5°	11.7
85°	6.7
87.5°	3.3
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)