

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205387

Luminaire Tested: **LSR6B15D010BZ EC6B10209030 6LBSLI1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P205387
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B15D010BZ EC6B10209030 6LBSLI1
Description: PORTFOLIO 6IN CYLINDER
SHALLOW DISTRIBUTION WITH SPECULAR CLEAR TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1350.3 lumens
Efficiency: N/A
Efficacy: 94.4 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1.04
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P205387

CATALOG NUMBER: LSR6B15D010BZ EC6B10209030 6LBSLI1

Luminous Intensity Polar Plot





TEST NUMBER: P205387

CATALOG NUMBER: LSR6B15D010BZ EC6B10209030 6LBSLI1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89			89
2	103	96	91	86	100	94	89	85	91	87	83	88	84	81	85	82	79	77			77
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	70	68			68
4	88	78	70	64	86	77	69	64	74	68	63	72	67	62	70	65	62	60			60
5	82	71	63	57	80	70	62	57	67	61	56	66	60	55	64	59	55	53			53
6	76	64	56	51	74	63	56	51	62	55	50	60	54	50	59	53	49	47			47
7	71	59	51	46	70	58	51	45	57	50	45	55	49	45	54	49	45	43			43
8	67	54	47	41	65	54	46	41	52	46	41	51	45	41	50	45	41	39			39
9	63	50	43	38	61	50	43	38	49	42	38	48	42	37	47	41	37	36			36
10	59	47	40	35	58	46	39	35	45	39	35	45	39	34	44	38	34	33			33

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P205387

CATALOG NUMBER: LSR6B15D010BZ EC6B10209030 6LBSLI1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.5	5.8
10°-20°	199.9	14.8
20°-30°	254.9	18.9
30°-40°	264.4	19.6
40°-50°	243.6	18.0
50°-60°	183.2	13.6
60°-70°	98.9	7.3
70°-80°	26.5	2.0
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	533.3	39.5
0°-40°	797.7	59.1
0°-60°	1224.5	90.7
0°-90°	1350.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1350.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	852	
5°	839	79
15°	713	200
25°	554	255
35°	422	264
45°	317	244
55°	205	183
65°	99	99
75°	23	27
85°	0	0
90°	0	



TEST NUMBER: P205387

CATALOG NUMBER: LSR6B15D010BZ EC6B10209030 6LBSLI1

CANDELA DISTRIBUTION (FULL):

	0°
0°	852.1
2.5°	849.2
5°	839.2
7.5°	820.6
10°	787.6
12.5°	754.6
15°	713.0
17.5°	674.2
20°	634.1
22.5°	592.5
25°	553.7
27.5°	516.4
30°	482.0
32.5°	450.4
35°	421.8
37.5°	394.5
40°	368.7
42.5°	341.4
45°	317.0
47.5°	289.8
50°	262.5
52.5°	233.8
55°	205.1
57.5°	176.4
60°	149.2
62.5°	123.4
65°	99.0
67.5°	76.0
70°	55.9
72.5°	38.7
75°	23.0
77.5°	10.0
80°	2.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)