

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204781

Luminaire Tested: **LSR6B15D010BZ EC6B10209730 6LBCSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204781
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B15D010BZ EC6B10209730 6LBCSMW1
Description: PORTFOLIO 6IN CYLINDER
SHALLOW DISTRIBUTION WITH CAST MATTE WHITE TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1201.8 lumens
Efficiency: N/A
Efficacy: 84.0 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204781

CATALOG NUMBER: LSR6B15D010BZ EC6B10209730 6LBCSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204781

CATALOG NUMBER: LSR6B15D010BZ EC6B10209730 6LBCSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	110	106	102	99	108	104	100	97	100	97	94	96	93	91	92	90	89	87																			
2	101	94	87	82	99	92	86	81	88	84	79	85	81	78	82	79	76	74																			
3	93	83	75	70	90	81	74	69	79	73	68	76	71	67	73	69	65	63																			
4	85	74	66	60	83	73	65	59	70	64	58	68	62	58	66	61	57	55																			
5	79	66	58	52	77	65	57	51	63	56	51	61	55	50	60	54	50	48																			
6	73	60	52	45	71	59	51	45	57	50	45	56	49	44	54	49	44	42																			
7	68	55	46	40	66	54	46	40	52	45	40	51	44	40	50	44	39	37																			
8	63	50	42	36	61	49	41	36	48	41	36	47	40	36	46	40	35	33																			
9	59	46	38	33	57	45	38	32	44	37	32	43	37	32	42	36	32	30																			
10	55	42	35	30	54	42	34	30	41	34	29	40	34	29	39	33	29	27																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204781

CATALOG NUMBER: LSR6B15D010BZ EC6B10209730 6LBCSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.5	3.9
10°-20°	132.4	11.0
20°-30°	199.2	16.6
30°-40°	236.0	19.6
40°-50°	234.9	19.5
50°-60°	189.4	15.8
60°-70°	114.6	9.5
70°-80°	42.5	3.5
80°-90°	6.3	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	378.1	31.5
0°-40°	614.1	51.1
0°-60°	1038.3	86.4
0°-90°	1201.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1201.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	491	
5°	489	47
15°	469	132
25°	433	199
35°	378	236
45°	306	235
55°	211	189
65°	115	115
75°	39	43
85°	5	6
90°	0	



TEST NUMBER: P204781

CATALOG NUMBER: LSR6B15D010BZ EC6B10209730 6LBCSMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	490.8
2.5°	490.8
5°	488.6
7.5°	487.2
10°	482.8
12.5°	475.5
15°	469.0
17.5°	461.7
20°	453.0
22.5°	444.2
25°	432.6
27.5°	420.2
30°	406.4
32.5°	393.2
35°	378.0
37.5°	361.9
40°	343.0
42.5°	324.8
45°	305.9
47.5°	284.7
50°	261.4
52.5°	237.4
55°	211.2
57.5°	187.9
60°	161.7
62.5°	138.4
65°	115.1
67.5°	93.2
70°	72.8
72.5°	54.6
75°	38.6
77.5°	24.8
80°	14.6
82.5°	8.7
85°	5.1
87.5°	2.2
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)