

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P795104

Luminaire Tested: LER6D65D010-EC6DR7055659040-6LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P795104
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LER6D65D010-EC6DR7055659040-6LBDP1H
Description: 6 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8455.1 lumens
Efficiency: N/A
Efficacy: 116.1 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct


Input Watts (W): 72.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



Downlight

TEST NUMBER: P795104
CATALOG NUMBER: LER6D65D010-EC6DR7055659040-6LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P795104

CATALOG NUMBER: LER6D65D010-EC6DR7055659040-6LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1038622
5°	1007766
10°	979678
15°	966817
20°	902812
25°	678235
30°	479459
35°	169836
40°	89301
45°	95121
50°	98486
55°	100350
60°	100979
65°	98837
70°	93281
75°	86414
80°	76700
85°	62305

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 101005 cd/sqm



TEST NUMBER: P795104

CATALOG NUMBER: LER6D65D010-EC6DR7055659040-6LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	866.7	10.3
10°-20°	2377.2	28.1
20°-30°	2618.2	31.0
30°-40°	1000.3	11.8
40°-50°	472.3	5.6
50°-60°	469.6	5.6
60°-70°	376.0	4.4
70°-80°	216.1	2.6
80°-90°	58.8	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5862.0	69.3
0°-40°	6862.4	81.2
0°-60°	7804.3	92.3
0°-90°	8455.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8455.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9506	
5°	9188	867
15°	8547	2377
25°	5626	2618
35°	1273	1000
45°	616	472
55°	527	470
65°	382	376
75°	205	216
85°	50	59
90°	0	



TEST NUMBER: P795104

CATALOG NUMBER: LER6D65D010-EC6DR7055659040-6LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	9505.9
2.5°	9406.6
5°	9188.4
7.5°	9006.2
10°	8830.2
12.5°	8681.2
15°	8547.2
17.5°	8223.6
20°	7764.6
22.5°	6774.3
25°	5625.9
27.5°	4897.4
30°	3800.3
32.5°	2454.7
35°	1273.3
37.5°	687.8
40°	626.1
42.5°	621.6
45°	615.6
47.5°	602.0
50°	579.4
52.5°	553.9
55°	526.8
57.5°	496.7
60°	462.1
62.5°	422.9
65°	382.3
67.5°	337.1
70°	292.0
72.5°	246.8
75°	204.7
77.5°	161.0
80°	121.9
82.5°	85.8
85°	49.7
87.5°	19.6
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)