

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P201215

Luminaire Tested: **LSR6B15D010BZ EC6B10208035 6LBM1LI**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P201215  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35151)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR6B15D010BZ EC6B10208035 6LBM1LI  
Description: PORTFOLIO 6IN CYLINDER  
MEDIUM DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1345.0 lumens  
Efficiency: N/A  
Efficacy: 94.1 lumens/watt  
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.85  
Luminous Opening: Circular (Dia: 1.12' x H: 0')  
CIE Type: Direct


Input Watts (W): 14.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P201215

CATALOG NUMBER: LSR6B15D010BZ EC6B10208035 6LBM1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P201215

CATALOG NUMBER: LSR6B15D010BZ EC6B10208035 6LBM1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94																			
2	108	103	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88																			
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	85	83	82																			
4	98	91	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76																			
5	93	85	79	75	91	84	79	75	82	78	74	81	77	73	79	76	73	71																			
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67																			
7	84	75	69	65	83	75	69	65	73	68	65	72	68	64	71	67	64	63																			
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	18227
5°	18053
10°	17108
15°	15532
20°	13725
25°	11866
30°	9275
35°	5688
40°	2919
45°	1159
50°	377
55°	130
60°	113
65°	87
70°	54
75°	71
80°	0
85°	0



TEST NUMBER: P201215

CATALOG NUMBER: LSR6B15D010BZ EC6B10208035 6LBM1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	155.1	11.5
10°-20°	386.1	28.7
20°-30°	448.8	33.4
30°-40°	274.8	20.4
40°-50°	68.2	5.1
50°-60°	8.0	0.6
60°-70°	2.9	0.2
70°-80°	1.1	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	989.9	73.6
0°-40°	1264.7	94.0
0°-60°	1340.9	99.7
0°-90°	1345.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1345.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1683	
5°	1661	155
15°	1386	386
25°	993	449
35°	430	275
45°	76	68
55°	7	8
65°	3	3
75°	2	1
85°	0	0
90°	0	



TEST NUMBER: P201215

CATALOG NUMBER: LSR6B15D010BZ EC6B10208035 6LBM1LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1683.2
2.5°	1681.5
5°	1660.8
7.5°	1616.1
10°	1555.9
12.5°	1476.7
15°	1385.5
17.5°	1287.4
20°	1191.0
22.5°	1094.6
25°	993.1
27.5°	876.0
30°	741.8
32.5°	585.2
35°	430.3
37.5°	302.9
40°	206.5
42.5°	129.1
45°	75.7
47.5°	43.0
50°	22.4
52.5°	10.3
55°	6.9
57.5°	5.2
60°	5.2
62.5°	3.4
65°	3.4
67.5°	1.7
70°	1.7
72.5°	1.7
75°	1.7
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)