

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203225

Luminaire Tested: **LSR6B15D010BZ EC6B10208040 6LBMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203225
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B15D010BZ EC6B10208040 6LBMH1
Description: PORTFOLIO 6IN CYLINDER
MEDIUM DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1110.2 lumens
Efficiency: N/A
Efficacy: 77.6 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.93
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203225

CATALOG NUMBER: LSR6B15D010BZ EC6B10208040 6LBMH1

Luminous Intensity Polar Plot





TEST NUMBER: P203225

CATALOG NUMBER: LSR6B15D010BZ EC6B10208040 6LBMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	92																																				
2	107	102	97	93	105	100	96	92	97	93	90	94	91	88	91	89	87	85																																				
3	101	94	88	84	99	92	87	84	90	86	82	87	84	81	85	82	80	78																																				
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72																																				
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66																																				
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61																																				
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																																				
8	76	66	60	55	75	65	59	55	64	59	55	63	58	55	62	58	54	53																																				
9	72	62	56	51	71	61	55	51	60	55	51	60	55	51	59	54	51	49																																				
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	55	51	48	46																																				

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203225

CATALOG NUMBER: LSR6B15D010BZ EC6B10208040 6LBMH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.5	9.0
10°-20°	259.9	23.4
20°-30°	336.7	30.3
30°-40°	250.0	22.5
40°-50°	105.5	9.5
50°-60°	37.5	3.4
60°-70°	14.5	1.3
70°-80°	5.0	0.5
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	697.1	62.8
0°-40°	947.1	85.3
0°-60°	1090.1	98.2
0°-90°	1110.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1110.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1099	
5°	1075	100
15°	928	260
25°	747	337
35°	396	250
45°	130	106
55°	40	37
65°	14	14
75°	5	5
85°	0	1
90°	0	



TEST NUMBER: P203225

CATALOG NUMBER: LSR6B15D010BZ EC6B10208040 6LBMH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1098.7
2.5°	1095.5
5°	1074.9
7.5°	1044.8
10°	1008.3
12.5°	968.7
15°	927.5
17.5°	881.5
20°	840.3
22.5°	797.4
25°	746.7
27.5°	677.0
30°	594.5
32.5°	497.8
35°	396.3
37.5°	310.7
40°	236.2
42.5°	176.0
45°	130.0
47.5°	95.1
50°	69.8
52.5°	52.3
55°	39.6
57.5°	30.1
60°	23.8
62.5°	17.4
65°	14.3
67.5°	11.1
70°	7.9
72.5°	6.3
75°	4.8
77.5°	3.2
80°	1.6
82.5°	1.6
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)