

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203328

Luminaire Tested: **LSR6B15D010BZ EC6B10208040 6LBMWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203328
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B15D010BZ EC6B10208040 6LBMWH1
Description: PORTFOLIO 6IN CYLINDER
MEDIUM DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1199.0 lumens
Efficiency: N/A
Efficacy: 83.8 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.85
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203328

CATALOG NUMBER: LSR6B15D010BZ EC6B10208040 6LBMWH1

Luminous Intensity Polar Plot





TEST NUMBER: P203328

CATALOG NUMBER: LSR6B15D010BZ EC6B10208040 6LBMWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	100	100		
	1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	97	96	95	94	94	94	94	94	94		
	2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	91	89	87	87	87	87	87	87		
	3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81	81	81	81	81	81		
	4	97	90	85	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76	76	76	76	76	76		
	5	93	84	79	74	91	83	78	74	82	77	73	80	76	73	78	75	72	71	71	71	71	71	71		
	6	88	79	73	69	87	78	73	69	77	72	68	76	71	68	74	70	67	66	66	66	66	66	66		
	7	84	75	69	64	82	74	68	64	73	68	64	71	67	64	70	66	63	62	62	62	62	62	62		
	8	80	70	64	60	78	70	64	60	69	64	60	68	63	60	67	62	59	58	58	58	58	58	58		
	9	76	66	61	57	75	66	60	57	65	60	56	64	59	56	63	59	56	55	55	55	55	55	55		
	10	72	63	57	53	71	62	57	53	62	57	53	61	56	53	60	56	53	52	52	52	52	52	52		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203328

CATALOG NUMBER: LSR6B15D010BZ EC6B10208040 6LBMWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	136.7	11.4
10°-20°	335.7	28.0
20°-30°	388.4	32.4
30°-40°	248.3	20.7
40°-50°	70.4	5.9
50°-60°	12.6	1.0
60°-70°	5.1	0.4
70°-80°	1.8	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	860.8	71.8
0°-40°	1109.1	92.5
0°-60°	1192.1	99.4
0°-90°	1199.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1199.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1496	
5°	1469	137
15°	1204	336
25°	857	388
35°	392	248
45°	82	70
55°	12	13
65°	5	5
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P203328

CATALOG NUMBER: LSR6B15D010BZ EC6B10208040 6LBMWH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	1495.7
2.5°	1494.0
5°	1469.0
7.5°	1424.0
10°	1360.6
12.5°	1287.3
15°	1203.9
17.5°	1117.2
20°	1032.2
22.5°	948.8
25°	857.1
27.5°	757.0
30°	645.3
32.5°	520.2
35°	391.9
37.5°	283.5
40°	196.8
42.5°	130.1
45°	81.7
47.5°	48.4
50°	28.3
52.5°	16.7
55°	11.7
57.5°	10.0
60°	8.3
62.5°	6.7
65°	5.0
67.5°	3.3
70°	3.3
72.5°	1.7
75°	1.7
77.5°	1.7
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)