

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204255

Luminaire Tested: **LSR6B15D010BZ EC6B10208040 6LBSWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204255
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B15D010BZ EC6B10208040 6LBSWH1
Description: PORTFOLIO 6IN CYLINDER
SHALLOW DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1590.5 lumens
Efficiency: N/A
Efficacy: 111.2 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1.08
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204255

CATALOG NUMBER: LSR6B15D010BZ EC6B10208040 6LBSWH1

Luminous Intensity Polar Plot





TEST NUMBER: P204255

CATALOG NUMBER: LSR6B15D010BZ EC6B10208040 6LBSWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89				89
2	103	96	90	85	100	94	89	84	91	86	83	87	84	81	85	82	79	77				77
3	95	86	79	73	93	84	78	73	82	76	72	79	74	70	76	73	69	67				67
4	88	77	70	64	86	76	69	63	74	68	63	72	66	62	69	65	61	59				59
5	81	70	62	56	79	69	62	56	67	60	55	65	59	55	63	58	54	52				52
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47				47
7	71	58	51	45	69	58	50	45	56	49	45	55	49	44	54	48	44	42				42
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38				38
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	37	35				35
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32				32

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204255

CATALOG NUMBER: LSR6B15D010BZ EC6B10208040 6LBSWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.5	5.5
10°-20°	226.4	14.2
20°-30°	296.2	18.6
30°-40°	313.6	19.7
40°-50°	292.5	18.4
50°-60°	221.6	13.9
60°-70°	120.0	7.5
70°-80°	32.2	2.0
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	610.1	38.4
0°-40°	923.7	58.1
0°-60°	1437.8	90.4
0°-90°	1590.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1590.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	948	
5°	935	87
15°	809	226
25°	644	296
35°	501	314
45°	381	293
55°	249	222
65°	120	120
75°	28	32
85°	0	0
90°	0	



TEST NUMBER: P204255

CATALOG NUMBER: LSR6B15D010BZ EC6B10208040 6LBSWH1

CANDELA DISTRIBUTION (FULL):

0°	
0°	948.5
2.5°	945.1
5°	934.6
7.5°	912.0
10°	882.4
12.5°	847.6
15°	809.3
17.5°	765.8
20°	727.5
22.5°	684.0
25°	644.0
27.5°	603.9
30°	565.6
32.5°	532.6
35°	501.2
37.5°	469.9
40°	440.3
42.5°	410.7
45°	381.2
47.5°	348.1
50°	315.0
52.5°	282.0
55°	248.9
57.5°	214.1
60°	181.0
62.5°	149.7
65°	120.1
67.5°	92.2
70°	67.9
72.5°	47.0
75°	27.8
77.5°	12.2
80°	3.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)