

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204261

Luminaire Tested: **LSR6B15D010BZ EC6B10209040 6LBSWH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P204261  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR6B15D010BZ EC6B10209040 6LBSWH1  
Description: PORTFOLIO 6IN CYLINDER  
SHALLOW DISTRIBUTION WITH WHEAT TRIM  
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W  
DL3-15.28 W DLE-15.432 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1332.5 lumens  
Efficiency: N/A  
Efficacy: 93.2 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1.08  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 14.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P204261

CATALOG NUMBER: LSR6B15D010BZ EC6B10209040 6LBSWH1

### Luminous Intensity Polar Plot





TEST NUMBER: P204261

CATALOG NUMBER: LSR6B15D010BZ EC6B10209040 6LBSWH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	94	92	90	89																			
2	103	96	90	85	100	94	89	84	91	86	83	87	84	81	85	82	79	77																			
3	95	86	79	73	93	84	78	73	82	76	72	79	74	70	76	73	69	67																			
4	88	77	70	64	86	76	69	63	74	68	63	72	66	62	69	65	61	59																			
5	81	70	62	56	79	69	62	56	67	60	55	65	59	55	63	58	54	52																			
6	76	64	56	50	74	63	55	50	61	54	49	60	54	49	58	53	49	47																			
7	71	58	51	45	69	58	50	45	56	49	45	55	49	44	54	48	44	42																			
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38																			
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	41	37	35																			
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32																			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P204261

CATALOG NUMBER: LSR6B15D010BZ EC6B10209040 6LBSWH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	73.3	5.5
10°-20°	189.7	14.2
20°-30°	248.2	18.6
30°-40°	262.8	19.7
40°-50°	245.0	18.4
50°-60°	185.6	13.9
60°-70°	100.5	7.5
70°-80°	27.0	2.0
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	511.2	38.4
0°-40°	773.9	58.1
0°-60°	1204.6	90.4
0°-90°	1332.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1332.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	795	
5°	783	73
15°	678	190
25°	540	248
35°	420	263
45°	319	245
55°	208	186
65°	101	101
75°	23	27
85°	0	0
90°	0	



TEST NUMBER: P204261

CATALOG NUMBER: LSR6B15D010BZ EC6B10209040 6LBSWH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	794.7
2.5°	791.8
5°	783.0
7.5°	764.1
10°	739.3
12.5°	710.1
15°	678.0
17.5°	641.6
20°	609.5
22.5°	573.1
25°	539.5
27.5°	506.0
30°	473.9
32.5°	446.2
35°	420.0
37.5°	393.7
40°	368.9
42.5°	344.1
45°	319.3
47.5°	291.6
50°	263.9
52.5°	236.2
55°	208.5
57.5°	179.4
60°	151.6
62.5°	125.4
65°	100.6
67.5°	77.3
70°	56.9
72.5°	39.4
75°	23.3
77.5°	10.2
80°	2.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)