

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204670

Luminaire Tested: **LSR6B15D010BZ EC6B10208050 6LBPSMW1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P204670  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR6B15D010BZ EC6B10208050 6LBPSMW1  
Description: PORTFOLIO 6IN CYLINDER  
SHALLOW DISTRIBUTION WITH PLASTIC MATTE WHITE TRIM  
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W  
DL3-15.28 W DLE-15.432 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1703.7 lumens  
Efficiency: N/A  
Efficacy: 119.1 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 14.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P204670

CATALOG NUMBER: LSR6B15D010BZ EC6B10208050 6LBPSMW1

### Luminous Intensity Polar Plot





TEST NUMBER: P204670

CATALOG NUMBER: LSR6B15D010BZ EC6B10208050 6LBPSMW1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86				86
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74				74
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63				63
4	85	74	65	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54				54
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47				47
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42				42
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37				37
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33				33
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30				30
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27				27

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P204670

CATALOG NUMBER: LSR6B15D010BZ EC6B10208050 6LBPSMW1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	65.0	3.8
10°-20°	185.4	10.9
20°-30°	279.2	16.4
30°-40°	332.2	19.5
40°-50°	331.6	19.5
50°-60°	269.7	15.8
60°-70°	165.9	9.7
70°-80°	64.3	3.8
80°-90°	10.3	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	529.6	31.1
0°-40°	861.9	50.6
0°-60°	1463.2	85.9
0°-90°	1703.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1703.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	686	
5°	684	65
15°	658	185
25°	608	279
35°	532	332
45°	431	332
55°	302	270
65°	167	166
75°	58	64
85°	8	10
90°	0	



TEST NUMBER: P204670

CATALOG NUMBER: LSR6B15D010BZ EC6B10208050 6LBPSMW1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	686.4
2.5°	687.4
5°	684.4
7.5°	680.4
10°	675.3
12.5°	666.2
15°	658.2
17.5°	646.0
20°	632.9
22.5°	620.8
25°	607.7
27.5°	589.5
30°	571.3
32.5°	554.2
35°	532.0
37.5°	507.8
40°	485.5
42.5°	458.3
45°	431.0
47.5°	401.8
50°	370.5
52.5°	338.2
55°	301.8
57.5°	266.5
60°	232.2
62.5°	198.9
65°	166.6
67.5°	136.3
70°	108.0
72.5°	81.8
75°	58.5
77.5°	38.4
80°	23.2
82.5°	14.1
85°	8.1
87.5°	4.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)