

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P175385

Luminaire Tested: **LDA6A10835D010TE LARL15SP 6LFC1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P175385
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26262)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A10835D010TE LARL15SP 6LFC1
Description: PORTFOLIO 6" Flat Cone, Self-flange Trim Ring, 15° Spot Optic, at 0° tilt
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 820.4 lumens
Efficiency: N/A
Efficacy: 59.3 lumens/watt
Spacing Criteria (0/90/45): 0.21 / 0.21 / 0.26
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 13.84
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P175385

CATALOG NUMBER: LDA6A10835D010TE LARL15SP 6LFC1

Luminous Intensity Polar Plot





TEST NUMBER: P175385

CATALOG NUMBER: LDA6A10835D010TE LARL15SP 6LFC1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97		
2	112	108	106	103	110	107	104	102	104	102	100	101	99	98	98	97	96	95		
3	109	104	101	98	107	103	100	98	101	98	96	98	96	95	96	95	93	92		
4	106	101	97	94	104	100	96	94	98	95	93	96	94	92	94	92	91	90		
5	103	97	94	91	102	97	93	90	95	92	90	94	91	89	92	90	88	87		
6	100	95	91	88	99	94	90	88	93	89	87	91	89	87	90	88	86	85		
7	98	92	88	85	97	91	88	85	90	87	85	89	86	84	88	86	84	83		
8	95	89	86	83	95	89	85	83	88	85	83	87	84	82	86	84	82	81		
9	93	87	83	81	92	87	83	81	86	83	81	85	82	80	85	82	80	79		
10	91	85	81	79	90	85	81	79	84	81	79	83	81	79	83	80	78	78		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	417686
5°	241833
10°	120901
15°	63071
20°	37500
25°	22876
30°	462
35°	114
40°	72
45°	54
50°	26
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P175385

CATALOG NUMBER: LDA6A10835D010TE LARL15SP 6LFC1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	352.6	43.0
10°-20°	319.9	39.0
20°-30°	145.8	17.8
30°-40°	1.5	0.2
40°-50°	0.4	0.1
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	818.4	99.8
0°-40°	819.9	99.9
0°-60°	820.4	100.0
0°-90°	820.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	820.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7619	
5°	4395	353
15°	1111	320
25°	378	146
35°	2	2
45°	1	0
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P175385

CATALOG NUMBER: LDA6A10835D010TE LARL15SP 6LFC1

CANDELA DISTRIBUTION (FULL):

	0°
0°	7619.2
1°	7255.2
2°	6538.0
3°	5749.4
4°	5025.3
5°	4394.6
6°	3844.5
7°	3356.9
8°	2920.7
9°	2534.2
10°	2171.9
11°	1850.7
12°	1580.5
13°	1380.8
14°	1232.5
15°	1111.3
17.5°	855.7
20°	642.8
22.5°	511.9
25°	378.2
27.5°	125.7
30°	7.3
32.5°	2.8
35°	1.7
37.5°	1.4
40°	1.0
42.5°	0.7
45°	0.7
47.5°	0.3
50°	0.3
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P175385

CATALOG NUMBER: LDA6A10835D010TE LARL15SP 6LFC1

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°	0.0
87.5°	0.0



(END OF REPORT)