

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203335

Luminaire Tested: **LSR6B15D010BZ EC6B10209050 6LBMWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203335
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B15D010BZ EC6B10209050 6LBMWH1
Description: PORTFOLIO 6IN CYLINDER
MEDIUM DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1008.3 lumens
Efficiency: N/A
Efficacy: 70.5 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.85
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203335

CATALOG NUMBER: LSR6B15D010BZ EC6B10209050 6LBMWH1

Luminous Intensity Polar Plot





TEST NUMBER: P203335

CATALOG NUMBER: LSR6B15D010BZ EC6B10209050 6LBMWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	97	96	95	94			
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	91	89	87			
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81			
4	97	90	85	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76			
5	93	84	79	74	91	83	78	74	82	77	73	80	76	73	78	75	72	71			
6	88	79	73	69	87	78	73	69	77	72	68	76	71	68	74	70	67	66			
7	84	75	69	64	82	74	68	64	73	68	64	71	67	64	70	66	63	62			
8	80	70	64	60	78	70	64	60	69	64	60	68	63	60	67	62	59	58			
9	76	66	61	57	75	66	60	57	65	60	56	64	59	56	63	59	56	55			
10	72	63	57	53	71	62	57	53	62	57	53	61	56	53	60	56	53	52			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203335

CATALOG NUMBER: LSR6B15D010BZ EC6B10209050 6LBMWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	115.0	11.4
10°-20°	282.3	28.0
20°-30°	326.6	32.4
30°-40°	208.8	20.7
40°-50°	59.2	5.9
50°-60°	10.6	1.0
60°-70°	4.3	0.4
70°-80°	1.5	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	723.9	71.8
0°-40°	932.7	92.5
0°-60°	1002.5	99.4
0°-90°	1008.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1008.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1258	
5°	1235	115
15°	1012	282
25°	721	327
35°	330	209
45°	69	59
55°	10	11
65°	4	4
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P203335

CATALOG NUMBER: LSR6B15D010BZ EC6B10209050 6LBMWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1257.8
2.5°	1256.4
5°	1235.4
7.5°	1197.5
10°	1144.3
12.5°	1082.6
15°	1012.4
17.5°	939.5
20°	868.0
22.5°	797.9
25°	720.8
27.5°	636.6
30°	542.7
32.5°	437.5
35°	329.5
37.5°	238.4
40°	165.5
42.5°	109.4
45°	68.7
47.5°	40.7
50°	23.8
52.5°	14.0
55°	9.8
57.5°	8.4
60°	7.0
62.5°	5.6
65°	4.2
67.5°	2.8
70°	2.8
72.5°	1.4
75°	1.4
77.5°	1.4
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)