

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204676

Luminaire Tested: **LSR6B15D010BZ EC6B10209050 6LBPSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204676
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B15D010BZ EC6B10209050 6LBPSMW1
Description: PORTFOLIO 6IN CYLINDER
SHALLOW DISTRIBUTION WITH PLASTIC MATTE WHITE TRIM
WATTAGE D010TR-14.39 W DE010-14.29 W D5LT-14.34 W DMX-14.46 W DL2-15.8 W
DL3-15.28 W DLE-15.432 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1433.5 lumens
Efficiency: N/A
Efficacy: 100.2 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204676

CATALOG NUMBER: LSR6B15D010BZ EC6B10209050 6LBPSMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204676

CATALOG NUMBER: LSR6B15D010BZ EC6B10209050 6LBPSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86				86
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74				74
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63				63
4	85	74	65	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54				54
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47				47
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42				42
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37				37
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33				33
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30				30
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27				27

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204676

CATALOG NUMBER: LSR6B15D010BZ EC6B10209050 6LBPSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.7	3.8
10°-20°	156.0	10.9
20°-30°	234.9	16.4
30°-40°	279.5	19.5
40°-50°	279.0	19.5
50°-60°	226.9	15.8
60°-70°	139.6	9.7
70°-80°	54.1	3.8
80°-90°	8.7	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	445.6	31.1
0°-40°	725.2	50.6
0°-60°	1231.1	85.9
0°-90°	1433.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1433.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	578	
5°	576	55
15°	554	156
25°	511	235
35°	448	280
45°	363	279
55°	254	227
65°	140	140
75°	49	54
85°	7	9
90°	0	



TEST NUMBER: P204676

CATALOG NUMBER: LSR6B15D010BZ EC6B10209050 6LBPSMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	577.6
2.5°	578.4
5°	575.9
7.5°	572.5
10°	568.2
12.5°	560.6
15°	553.8
17.5°	543.6
20°	532.5
22.5°	522.4
25°	511.3
27.5°	496.0
30°	480.7
32.5°	466.3
35°	447.6
37.5°	427.2
40°	408.5
42.5°	385.6
45°	362.7
47.5°	338.0
50°	311.7
52.5°	284.5
55°	254.0
57.5°	224.2
60°	195.4
62.5°	167.3
65°	140.1
67.5°	114.7
70°	90.9
72.5°	68.8
75°	49.3
77.5°	32.3
80°	19.5
82.5°	11.9
85°	6.8
87.5°	3.4
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)