

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203137

Luminaire Tested: **LSR6B20D010BZ EC6B10209024 6LBWMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203137
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B20D010BZ EC6B10209024 6LBWMW1
Description: PORTFOLIO 6IN CYLINDER
WIDE DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1391.7 lumens
Efficiency: N/A
Efficacy: 66.9 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.13 / 1.15
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203137

CATALOG NUMBER: LSR6B20D010BZ EC6B10209024 6LBWMW1

Luminous Intensity Polar Plot





TEST NUMBER: P203137

CATALOG NUMBER: LSR6B20D010BZ EC6B10209024 6LBWMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88																			
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77																			
3	95	86	80	74	93	85	79	74	82	77	72	80	75	71	77	73	70	68																			
4	89	78	71	65	86	77	70	65	75	69	64	72	67	63	70	66	62	60																			
5	82	71	64	58	80	70	63	58	68	62	57	66	61	56	65	60	56	54																			
6	77	65	57	52	75	64	57	52	63	56	51	61	55	51	60	54	50	49																			
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44																			
8	67	55	48	42	66	55	47	42	53	47	42	52	46	42	51	46	42	40																			
9	63	51	44	39	62	51	44	39	50	43	39	49	43	38	48	42	38	37																			
10	60	48	40	36	58	47	40	36	46	40	36	45	40	35	45	39	35	34																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203137

CATALOG NUMBER: LSR6B20D010BZ EC6B10209024 6LBWMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.6	5.3
10°-20°	206.4	14.8
20°-30°	297.4	21.4
30°-40°	308.8	22.2
40°-50°	228.3	16.4
50°-60°	136.3	9.8
60°-70°	82.9	6.0
70°-80°	45.4	3.3
80°-90°	12.6	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	577.4	41.5
0°-40°	886.2	63.7
0°-60°	1250.8	89.9
0°-90°	1391.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1391.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	782	
5°	776	74
15°	733	206
25°	648	297
35°	498	309
45°	294	228
55°	148	136
65°	83	83
75°	42	45
85°	10	13
90°	0	



TEST NUMBER: P203137

CATALOG NUMBER: LSR6B20D010BZ EC6B10209024 6LBWMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	781.6
2.5°	781.6
5°	776.5
7.5°	769.8
10°	759.6
12.5°	747.8
15°	732.6
17.5°	715.7
20°	698.9
22.5°	675.2
25°	648.2
27.5°	619.5
30°	582.4
32.5°	545.2
35°	498.0
37.5°	449.0
40°	395.0
42.5°	342.7
45°	293.7
47.5°	249.8
50°	211.0
52.5°	177.2
55°	148.5
57.5°	126.6
60°	108.0
62.5°	94.5
65°	82.7
67.5°	72.6
70°	62.5
72.5°	52.3
75°	42.2
77.5°	33.8
80°	25.3
82.5°	18.6
85°	10.1
87.5°	5.1
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)