

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204059

Luminaire Tested: **LSR6B20D010BZ EC6B10208027 6LBNMW1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P204059  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR6B20D010BZ EC6B10208027 6LBNMW1  
Description: PORTFOLIO 6IN CYLINDER  
NARROW DISTRIBUTION WITH MATTE WHITE TRIM  
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W  
DL3-21.8 6 W DLE-22.46 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1407.4 lumens  
Efficiency: N/A  
Efficacy: 67.7 lumens/watt  
Spacing Criteria (0/90/45): 0.99 / 0.99 / 0.97  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 20.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P204059

CATALOG NUMBER: LSR6B20D010BZ EC6B10208027 6LBNMW1

### Luminous Intensity Polar Plot





TEST NUMBER: P204059

CATALOG NUMBER: LSR6B20D010BZ EC6B10208027 6LBNMW1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |    |    |    |    |    |    |    |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|----|----|----|----|----|----|----|----|----|---|--|--|--|--|--|--|----|--|--|--|--|--|--|--|--|
| RF  | 20  |     |     |     |     |     |     |     |     | 20  |     |     |     |     |     |     |     |     | 20 |    |    |    |    |    |    |    |    | 20 |    |   |  |  |  |  |  |  | 20 |  |  |  |  |  |  |  |  |
| RC  | 80  |     |     |     |     |     |     |     |     | 50  |     |     |     |     |     |     |     |     | 30 |    |    |    |    |    |    |    |    | 10 |    |   |  |  |  |  |  |  | 0  |  |  |  |  |  |  |  |  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |    |    |    |    |    |    |    |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |    |    |    |    |    |    |    |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |
| 1   | 112 | 108 | 105 | 103 | 109 | 106 | 103 | 101 | 102 | 100 | 98  | 98  | 97  | 95  | 95  | 93  | 92  | 90  |    |    |    |    |    |    |    |    |    |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |
| 2   | 105 | 99  | 94  | 90  | 102 | 97  | 92  | 89  | 94  | 90  | 87  | 91  | 87  | 85  | 88  | 85  | 83  | 81  |    |    |    |    |    |    |    |    |    |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |
| 3   | 98  | 90  | 84  | 79  | 96  | 89  | 83  | 79  | 86  | 81  | 77  | 84  | 80  | 76  | 81  | 78  | 75  | 73  |    |    |    |    |    |    |    |    |    |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |
| 4   | 92  | 83  | 76  | 71  | 90  | 82  | 76  | 71  | 80  | 74  | 70  | 77  | 73  | 69  | 75  | 71  | 68  | 66  |    |    |    |    |    |    |    |    |    |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |
| 5   | 87  | 77  | 70  | 64  | 85  | 76  | 69  | 64  | 74  | 68  | 64  | 72  | 67  | 63  | 70  | 66  | 62  | 61  |    |    |    |    |    |    |    |    |    |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |
| 6   | 81  | 71  | 64  | 59  | 80  | 70  | 63  | 59  | 68  | 63  | 58  | 67  | 62  | 58  | 66  | 61  | 57  | 56  |    |    |    |    |    |    |    |    |    |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |
| 7   | 77  | 66  | 59  | 54  | 75  | 65  | 59  | 54  | 64  | 58  | 54  | 63  | 57  | 53  | 61  | 57  | 53  | 51  |    |    |    |    |    |    |    |    |    |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |
| 8   | 72  | 61  | 55  | 50  | 71  | 61  | 54  | 50  | 60  | 54  | 49  | 59  | 53  | 49  | 58  | 53  | 49  | 47  |    |    |    |    |    |    |    |    |    |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |
| 9   | 69  | 58  | 51  | 46  | 67  | 57  | 51  | 46  | 56  | 50  | 46  | 55  | 50  | 46  | 54  | 49  | 46  | 44  |    |    |    |    |    |    |    |    |    |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |
| 10  | 65  | 54  | 47  | 43  | 64  | 54  | 47  | 43  | 53  | 47  | 43  | 52  | 46  | 43  | 51  | 46  | 43  | 41  |    |    |    |    |    |    |    |    |    |    |    |   |  |  |  |  |  |  |    |  |  |  |  |  |  |  |  |

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P204059

CATALOG NUMBER: LSR6B20D010BZ EC6B10208027 6LBNMW1

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 107.2  | 7.6       |
| 10°-20°   | 284.1  | 20.2      |
| 20°-30°   | 379.3  | 26.9      |
| 30°-40°   | 306.0  | 21.7      |
| 40°-50°   | 146.7  | 10.4      |
| 50°-60°   | 86.9   | 6.2       |
| 60°-70°   | 57.8   | 4.1       |
| 70°-80°   | 31.0   | 2.2       |
| 80°-90°   | 8.5    | 0.6       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 770.6  | 54.8      |
| 0°-40°    | 1076.6 | 76.5      |
| 0°-60°    | 1310.2 | 93.1      |
| 0°-90°    | 1407.4 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1407.4 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1154 |      |
| 5°  | 1141 | 107  |
| 15° | 1011 | 284  |
| 25° | 830  | 379  |
| 35° | 490  | 306  |
| 45° | 181  | 147  |
| 55° | 96   | 87   |
| 65° | 58   | 58   |
| 75° | 29   | 31   |
| 85° | 7    | 8    |
| 90° | 0    |      |



TEST NUMBER: P204059

CATALOG NUMBER: LSR6B20D010BZ EC6B10208027 6LBNMW1

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 1154.3 |
| 2.5°  | 1154.3 |
| 5°    | 1140.8 |
| 7.5°  | 1118.5 |
| 10°   | 1087.1 |
| 12.5° | 1053.6 |
| 15°   | 1011.1 |
| 17.5° | 970.8  |
| 20°   | 926.1  |
| 22.5° | 879.1  |
| 25°   | 829.9  |
| 27.5° | 778.5  |
| 30°   | 704.6  |
| 32.5° | 601.7  |
| 35°   | 489.9  |
| 37.5° | 387.0  |
| 40°   | 299.7  |
| 42.5° | 232.6  |
| 45°   | 181.2  |
| 47.5° | 143.2  |
| 50°   | 120.8  |
| 52.5° | 107.4  |
| 55°   | 96.2   |
| 57.5° | 87.2   |
| 60°   | 76.1   |
| 62.5° | 67.1   |
| 65°   | 58.2   |
| 67.5° | 49.2   |
| 70°   | 42.5   |
| 72.5° | 35.8   |
| 75°   | 29.1   |
| 77.5° | 22.4   |
| 80°   | 17.9   |
| 82.5° | 13.4   |
| 85°   | 6.7    |
| 87.5° | 2.2    |
| 90°   | 0.0    |



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)