

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P175519

Luminaire Tested: **LDA6A15827D010TE LAR35FL 6LFC1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P175519  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26295)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LDA6A15827D010TE LAR35FL 6LFC1  
Description: PORTFOLIO 6" Flat Cone, Self-flange Trim Ring, 35° Flood Optic, at 0° tilt  
Light Source: (1) HIGH LUMEN LED 80CRI / 2700K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1218.5 lumens  
Efficiency: N/A  
Efficacy: 54.7 lumens/watt  
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.56  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct


Input Watts (W): 22.27  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P175519

CATALOG NUMBER: LDA6A15827D010TE LAR35FL 6LFC1

### Luminous Intensity Polar Plot





TEST NUMBER: P175519

CATALOG NUMBER: LDA6A15827D010TE LAR35FL 6LFC1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	115	113	111	109	112	111	109	107	107	105	104	103	102	101	100	99	98	96	96	98	96																
2	111	107	104	101	109	105	103	100	102	100	98	99	98	96	97	95	94	93			93																
3	107	102	99	96	105	101	98	95	98	96	93	96	94	92	94	92	91	89			89																
4	104	98	94	91	102	97	93	90	95	92	89	93	90	88	91	89	87	86			86																
5	100	94	90	87	99	93	89	86	92	88	85	90	87	85	89	86	84	83			83																
6	97	90	86	83	96	90	86	83	88	85	82	87	84	82	86	83	81	80			80																
7	94	87	83	80	93	87	82	79	85	82	79	84	81	79	83	81	78	77			77																
8	91	84	80	77	90	84	79	77	83	79	76	82	78	76	81	78	76	75			75																
9	88	81	77	74	87	81	77	74	80	76	74	79	76	73	79	76	73	72			72																
10	86	79	74	72	85	78	74	71	78	74	71	77	74	71	76	73	71	70			70																

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	196295
5°	187326
10°	160034
15°	131022
20°	83861
25°	32306
30°	6621
35°	1760
40°	551
45°	178
50°	77
55°	48
60°	55
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P175519

CATALOG NUMBER: LDA6A15827D010TE LAR35FL 6LFC1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	306.6	25.2
10°-20°	616.3	50.6
20°-30°	270.1	22.2
30°-40°	22.6	1.9
40°-50°	2.3	0.2
50°-60°	0.5	0.0
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1193.0	97.9
0°-40°	1215.6	99.8
0°-60°	1218.3	100.0
0°-90°	1218.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1218.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3581	
5°	3404	307
15°	2309	616
25°	534	270
35°	26	23
45°	2	2
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P175519

CATALOG NUMBER: LDA6A15827D010TE LAR35FL 6LFC1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3580.7
1°	3563.5
2°	3535.4
3°	3503.3
4°	3462.5
5°	3404.1
6°	3320.7
7°	3212.9
8°	3094.6
9°	2982.3
10°	2874.9
11°	2767.1
12°	2662.0
13°	2552.8
14°	2436.8
15°	2308.6
17.5°	1914.5
20°	1437.5
22.5°	938.7
25°	534.1
27.5°	248.7
30°	104.6
32.5°	54.4
35°	26.3
37.5°	14.0
40°	7.7
42.5°	4.1
45°	2.3
47.5°	1.4
50°	0.9
52.5°	0.5
55°	0.5
57.5°	0.5
60°	0.5
62.5°	0.5
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P175519

CATALOG NUMBER: LDA6A15827D010TE LAR35FL 6LFC1

**CANDELA DISTRIBUTION (continued):**

0°  
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)