

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P202932

Luminaire Tested: **LSR6B20D010BZ EC6B10209027 6LBWGPH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P202932
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B20D010BZ EC6B10209027 6LBWGPH1
Description: PORTFOLIO 6IN CYLINDER
WIDE DISTRIBUTIONWITH GRAPHITE HAZE TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1114.0 lumens
Efficiency: N/A
Efficacy: 53.6 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.11
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P202932

CATALOG NUMBER: LSR6B20D010BZ EC6B10209027 6LBWGPH1

Luminous Intensity Polar Plot





TEST NUMBER: P202932

CATALOG NUMBER: LSR6B20D010BZ EC6B10209027 6LBWGPH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	82																			
3	99	91	85	81	97	90	84	80	87	82	79	85	81	77	82	79	76	74																			
4	93	84	77	72	91	82	76	72	80	75	71	78	74	70	76	72	69	67																			
5	87	77	70	65	85	76	69	65	74	68	64	72	67	63	71	66	63	61																			
6	81	71	64	59	80	70	63	59	68	62	58	67	62	58	65	61	57	56																			
7	76	65	58	53	75	65	58	53	63	57	53	62	57	53	61	56	52	51																			
8	72	61	54	49	70	60	53	49	59	53	49	58	52	48	57	52	48	47																			
9	68	57	50	45	66	56	49	45	55	49	45	54	48	45	53	48	44	43																			
10	64	53	46	42	63	52	46	42	51	45	41	51	45	41	50	45	41	40																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P202932

CATALOG NUMBER: LSR6B20D010BZ EC6B10209027 6LBWGPH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	71.3	6.4
10°-20°	200.0	18.0
20°-30°	286.2	25.7
30°-40°	285.3	25.6
40°-50°	181.6	16.3
50°-60°	67.0	6.0
60°-70°	16.8	1.5
70°-80°	5.0	0.5
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	557.5	50.0
0°-40°	842.8	75.7
0°-60°	1091.4	98.0
0°-90°	1114.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1114.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	757	
5°	753	71
15°	711	200
25°	625	286
35°	464	285
45°	234	182
55°	71	67
65°	15	17
75°	4	5
85°	0	1
90°	0	



TEST NUMBER: P202932

CATALOG NUMBER: LSR6B20D010BZ EC6B10209027 6LBWGPH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	757.1
2.5°	757.1
5°	753.3
7.5°	745.6
10°	736.1
12.5°	724.6
15°	711.1
17.5°	693.9
20°	674.7
22.5°	653.6
25°	624.9
27.5°	594.2
30°	554.0
32.5°	511.8
35°	463.9
37.5°	406.4
40°	346.9
42.5°	289.4
45°	233.8
47.5°	184.0
50°	138.0
52.5°	101.6
55°	70.9
57.5°	46.0
60°	30.7
62.5°	21.1
65°	15.3
67.5°	11.5
70°	9.6
72.5°	5.8
75°	3.8
77.5°	3.8
80°	1.9
82.5°	1.9
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)