

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P175520

Luminaire Tested: **LDA6A15830D010TE LAR35FL 6LFC1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P175520
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26295)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A15830D010TE LAR35FL 6LFC1
Description: PORTFOLIO 6" Flat Cone, Self-flange Trim Ring, 35° Flood Optic, at 0° tilt
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1319.0 lumens
Efficiency: N/A
Efficacy: 59.2 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.56
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 22.27
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P175520

CATALOG NUMBER: LDA6A15830D010TE LAR35FL 6LFC1

Luminous Intensity Polar Plot





TEST NUMBER: P175520

CATALOG NUMBER: LDA6A15830D010TE LAR35FL 6LFC1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	113	111	109	112	111	109	107	107	105	104	103	102	101	100	99	98	96	96	96	96
2	111	107	104	101	109	105	103	100	102	100	98	99	98	96	97	95	94	93	93	93	93
3	107	102	99	96	105	101	98	95	98	96	93	96	94	92	94	92	91	89	89	89	89
4	104	98	94	91	102	97	93	90	95	92	89	93	90	88	91	89	87	86	86	86	86
5	100	94	90	87	99	93	89	86	92	88	85	90	87	85	89	86	84	83	83	83	83
6	97	90	86	83	96	90	86	83	88	85	82	87	84	82	86	83	81	80	80	80	80
7	94	87	83	80	93	87	82	79	85	82	79	84	81	79	83	81	78	77	77	77	77
8	91	84	80	77	90	84	79	77	83	79	76	82	78	76	81	78	76	75	75	75	75
9	88	81	77	74	87	81	77	74	80	76	74	79	76	73	79	76	73	72	72	72	72
10	86	79	74	72	85	78	74	71	78	74	71	77	74	71	76	73	71	70	70	70	70

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	212494
5°	202778
10°	173238
15°	141834
20°	90780
25°	34974
30°	7172
35°	1901
40°	594
45°	194
50°	85
55°	48
60°	55
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P175520

CATALOG NUMBER: LDA6A15830D010TE LAR35FL 6LFC1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	331.9	25.2
10°-20°	667.1	50.6
20°-30°	292.4	22.2
30°-40°	24.4	1.9
40°-50°	2.5	0.2
50°-60°	0.5	0.0
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1291.4	97.9
0°-40°	1315.8	99.8
0°-60°	1318.8	100.0
0°-90°	1319.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1319.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3876	
5°	3685	332
15°	2499	667
25°	578	292
35°	28	24
45°	2	2
55°	0	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P175520

CATALOG NUMBER: LDA6A15830D010TE LAR35FL 6LFC1

CANDELA DISTRIBUTION (FULL):

	0°
0°	3876.2
1°	3857.5
2°	3827.1
3°	3792.3
4°	3748.2
5°	3684.9
6°	3594.7
7°	3478.0
8°	3350.0
9°	3228.4
10°	3112.1
11°	2995.4
12°	2881.6
13°	2763.4
14°	2637.9
15°	2499.1
17.5°	2072.5
20°	1556.1
22.5°	1016.1
25°	578.2
27.5°	269.2
30°	113.3
32.5°	58.8
35°	28.4
37.5°	15.2
40°	8.3
42.5°	4.4
45°	2.5
47.5°	1.5
50°	1.0
52.5°	0.5
55°	0.5
57.5°	0.5
60°	0.5
62.5°	0.5
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P175520

CATALOG NUMBER: LDA6A15830D010TE LAR35FL 6LFC1

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)