

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P202829

Luminaire Tested: **LSR6B20D010BZ EC6B10209027 6LBWWH1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P202829  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR6B20D010BZ EC6B10209027 6LBWWH1  
Description: PORTFOLIO 6IN CYLINDER  
WIDE DISTRIBUTION WITH WHEAT TRIM  
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W  
DL3-21.8 6 W DLE-22.46 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1530.0 lumens  
Efficiency: N/A  
Efficacy: 73.6 lumens/watt  
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.18  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 20.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P202829

CATALOG NUMBER: LSR6B20D010BZ EC6B10209027 6LBWWH1

### Luminous Intensity Polar Plot





TEST NUMBER: P202829

CATALOG NUMBER: LSR6B20D010BZ EC6B10209027 6LBWWH1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92																			
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83																			
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75																			
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	68																			
5	87	77	71	66	85	76	70	65	75	69	65	73	68	64	71	67	63	62																			
6	82	71	64	59	80	71	64	59	69	63	59	67	62	58	66	61	58	56																			
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51																			
8	72	61	54	49	71	61	54	49	59	53	49	58	53	49	57	52	49	47																			
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43																			
10	64	53	46	42	63	53	46	42	52	46	42	51	45	42	50	45	41	40																			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P202829

CATALOG NUMBER: LSR6B20D010BZ EC6B10209027 6LBWWH1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	91.3	6.0
10°-20°	271.6	17.8
20°-30°	408.9	26.7
30°-40°	418.1	27.3
40°-50°	253.9	16.6
50°-60°	71.5	4.7
60°-70°	10.9	0.7
70°-80°	3.5	0.2
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	771.9	50.4
0°-40°	1190.0	77.8
0°-60°	1515.4	99.0
0°-90°	1530.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1530.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	950	
5°	954	91
15°	962	272
25°	893	409
35°	678	418
45°	326	254
55°	71	71
65°	10	11
75°	4	4
85°	0	0
90°	0	



TEST NUMBER: P202829

CATALOG NUMBER: LSR6B20D010BZ EC6B10209027 6LBWWH1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	950.3
2.5°	950.3
5°	954.2
7.5°	959.9
10°	959.9
12.5°	963.8
15°	961.9
17.5°	958.0
20°	944.6
22.5°	925.4
25°	892.7
27.5°	856.3
30°	806.4
32.5°	746.8
35°	677.7
37.5°	600.9
40°	512.6
42.5°	420.5
45°	326.4
47.5°	241.9
50°	170.9
52.5°	115.2
55°	71.0
57.5°	42.2
60°	21.1
62.5°	13.4
65°	9.6
67.5°	7.7
70°	5.8
72.5°	3.8
75°	3.8
77.5°	1.9
80°	1.9
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)