

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P175429

Luminaire Tested: **LDA6A15935D010TE LARL20NF 6LFC1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P175429
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26263)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A15935D010TE LARL20NF 6LFC1
Description: PORTFOLIO 6" Flat Cone, Self-flange Trim Ring, 20° Narrow Flood Optic, at 0° tilt
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1138.8 lumens
Efficiency: N/A
Efficacy: 51.1 lumens/watt
Spacing Criteria (0/90/45): 0.35 / 0.35 / 0.34
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 22.27
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P175429

CATALOG NUMBER: LDA6A15935D010TE LARL20NF 6LFC1

Luminous Intensity Polar Plot





TEST NUMBER: P175429

CATALOG NUMBER: LDA6A15935D010TE LARL20NF 6LFC1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	99	100
1	115	114	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97	97	98	97
2	112	109	106	104	110	107	105	103	104	102	101	101	100	98	99	98	96	95	99	98	96
3	109	105	102	99	107	104	101	98	101	99	97	99	97	95	97	95	94	93	97	95	94
4	106	102	98	95	105	101	97	95	99	96	94	97	95	93	95	93	92	91	95	93	92
5	104	99	95	92	102	98	94	92	96	93	91	95	92	90	93	91	90	89	93	91	90
6	101	96	92	90	100	95	92	89	94	91	89	93	90	88	92	89	88	87	92	89	88
7	99	93	90	87	98	93	89	87	92	89	87	91	88	86	90	87	86	85	90	87	86
8	97	91	87	85	96	91	87	85	90	87	85	89	86	84	88	86	84	83	88	86	84
9	95	89	85	83	94	89	85	83	88	85	83	87	84	82	86	84	82	81	86	84	82
10	93	87	84	81	92	87	83	81	86	83	81	85	83	81	85	82	81	80	85	82	81

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	413377
5°	341778
10°	219791
15°	89598
20°	42768
25°	16023
30°	1152
35°	228
40°	93
45°	31
50°	34
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P175429

CATALOG NUMBER: LDA6A15935D010TE LARL20NF 6LFC1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	523.8	46.0
10°-20°	479.8	42.1
20°-30°	131.5	11.5
30°-40°	3.2	0.3
40°-50°	0.5	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1135.0	99.7
0°-40°	1138.2	100.0
0°-60°	1138.8	100.0
0°-90°	1138.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1138.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7541	
5°	6211	524
15°	1579	480
25°	265	132
35°	3	3
45°	0	0
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P175429

CATALOG NUMBER: LDA6A15935D010TE LARL20NF 6LFC1

CANDELA DISTRIBUTION (FULL):

	0°
0°	7540.6
1°	7430.8
2°	7186.9
3°	6889.0
4°	6554.8
5°	6210.8
6°	5848.3
7°	5456.1
8°	5008.2
9°	4504.9
10°	3948.4
11°	3360.2
12°	2812.2
13°	2317.3
14°	1915.9
15°	1578.7
17.5°	1011.6
20°	733.1
22.5°	495.7
25°	264.9
27.5°	88.7
30°	18.2
32.5°	6.3
35°	3.4
37.5°	2.1
40°	1.3
42.5°	0.8
45°	0.4
47.5°	0.4
50°	0.4
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0



TEST NUMBER: P175429

CATALOG NUMBER: LDA6A15935D010TE LARL20NF 6LFC1

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)