

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203555

Luminaire Tested: **LSR6B20D010BZ EC6B10209727 6LBMMW1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P203555  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR6B20D010BZ EC6B10209727 6LBMMW1  
Description: PORTFOLIO 6IN CYLINDER  
MEDIUM DISTRIBUTION WITH MATTE WHITE TRIM  
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W  
DL3-21.8 6 W DLE-22.46 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1167.4 lumens  
Efficiency: N/A  
Efficacy: 56.1 lumens/watt  
Spacing Criteria (0/90/45): 1 / 1 / 0.97  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 20.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P203555

CATALOG NUMBER: LSR6B20D010BZ EC6B10209727 6LBMMW1

### Luminous Intensity Polar Plot





TEST NUMBER: P203555

CATALOG NUMBER: LSR6B20D010BZ EC6B10209727 6LBMMW1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	108	104	101	109	105	103	100	101	99	97	98	96	94	94	92	91	89
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71
4	90	81	74	68	88	80	73	68	77	72	67	75	70	66	73	69	65	64
5	85	74	67	61	83	73	66	61	71	65	61	69	64	60	68	63	59	58
6	79	68	61	56	78	68	61	56	66	60	55	64	59	55	63	58	54	53
7	75	63	56	51	73	63	56	51	61	55	50	60	54	50	59	54	50	48
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	43	41
10	63	51	45	40	62	51	44	40	50	44	40	49	44	40	48	43	40	38

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P203555

CATALOG NUMBER: LSR6B20D010BZ EC6B10209727 6LBMMW1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	80.5	6.9
10°-20°	215.5	18.5
20°-30°	289.4	24.8
30°-40°	237.4	20.3
40°-50°	142.5	12.2
50°-60°	94.7	8.1
60°-70°	63.5	5.4
70°-80°	34.2	2.9
80°-90°	9.6	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	585.4	50.1
0°-40°	822.8	70.5
0°-60°	1060.1	90.8
0°-90°	1167.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1167.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	871	
5°	857	80
15°	768	216
25°	638	289
35°	377	237
45°	180	143
55°	105	95
65°	64	63
75°	32	34
85°	8	10
90°	0	



TEST NUMBER: P203555

CATALOG NUMBER: LSR6B20D010BZ EC6B10209727 6LBMMW1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	871.1
2.5°	864.6
5°	856.6
7.5°	838.9
10°	817.9
12.5°	792.2
15°	768.0
17.5°	739.0
20°	710.1
22.5°	677.9
25°	637.6
27.5°	589.3
30°	524.9
32.5°	452.4
35°	376.8
37.5°	312.4
40°	257.6
42.5°	214.1
45°	180.3
47.5°	153.0
50°	133.6
52.5°	117.5
55°	104.7
57.5°	93.4
60°	83.7
62.5°	72.5
65°	64.4
67.5°	54.7
70°	46.7
72.5°	38.6
75°	32.2
77.5°	25.8
80°	19.3
82.5°	14.5
85°	8.1
87.5°	3.2
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)