

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204070

Luminaire Tested: **LSR6B20D010BZ EC6B10209727 6LBNMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204070
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B20D010BZ EC6B10209727 6LBNMW1
Description: PORTFOLIO 6IN CYLINDER
NARROW DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1050.7 lumens
Efficiency: N/A
Efficacy: 50.5 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.99 / 0.97
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204070

CATALOG NUMBER: LSR6B20D010BZ EC6B10209727 6LBNMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204070

CATALOG NUMBER: LSR6B20D010BZ EC6B10209727 6LBNMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	103	109	106	103	101	102	100	98	98	97	95	95	93	92	90		
2	105	99	94	90	102	97	92	89	94	90	87	91	87	85	88	85	83	81		
3	98	90	84	79	96	89	83	79	86	81	77	84	80	76	81	78	75	73		
4	92	83	76	71	90	82	76	71	80	74	70	77	73	69	75	71	68	66		
5	87	77	70	64	85	76	69	64	74	68	64	72	67	63	70	66	62	61		
6	81	71	64	59	80	70	63	59	68	63	58	67	62	58	66	61	57	56		
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51		
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47		
9	69	58	51	46	67	57	51	46	56	50	46	55	50	46	54	49	46	44		
10	65	54	47	43	64	54	47	43	53	47	43	52	46	43	51	46	43	41		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204070

CATALOG NUMBER: LSR6B20D010BZ EC6B10209727 6LBNMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	80.0	7.6
10°-20°	212.1	20.2
20°-30°	283.1	26.9
30°-40°	228.4	21.7
40°-50°	109.5	10.4
50°-60°	64.9	6.2
60°-70°	43.1	4.1
70°-80°	23.1	2.2
80°-90°	6.4	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	575.2	54.7
0°-40°	803.7	76.5
0°-60°	978.1	93.1
0°-90°	1050.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1050.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	862	
5°	852	80
15°	755	212
25°	620	283
35°	366	228
45°	135	110
55°	72	65
65°	43	43
75°	22	23
85°	5	6
90°	0	



TEST NUMBER: P204070

CATALOG NUMBER: LSR6B20D010BZ EC6B10209727 6LBNMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	861.7
2.5°	861.7
5°	851.6
7.5°	834.9
10°	811.6
12.5°	786.5
15°	754.8
17.5°	724.7
20°	691.3
22.5°	656.3
25°	619.5
27.5°	581.1
30°	526.0
32.5°	449.2
35°	365.7
37.5°	288.9
40°	223.8
42.5°	173.7
45°	135.3
47.5°	106.9
50°	90.2
52.5°	80.2
55°	71.8
57.5°	65.1
60°	56.8
62.5°	50.1
65°	43.4
67.5°	36.7
70°	31.7
72.5°	26.7
75°	21.7
77.5°	16.7
80°	13.4
82.5°	10.0
85°	5.0
87.5°	1.7
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)