

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P179553

Luminaire Tested: **LDA6A45930D010TE LARH20SP 6LA1LI**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P179553  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26660)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LDA6A45930D010TE LARH20SP 6LA1LI  
Description: PORTFOLIO 6" Adjustable Reflector, Angle-cut Trim, Self-flanged, 20° Spot  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3445.7 lumens  
Efficiency: N/A  
Efficacy: 65.0 lumens/watt  
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.49  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct


Input Watts (W): 53  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P179553

CATALOG NUMBER: LDA6A45930D010TE LARH20SP 6LA1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P179553

CATALOG NUMBER: LDA6A45930D010TE LARH20SP 6LA1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100											100																	
1	115	113	111	109	113	111	109	107	107	105	104	103	102	101	100	99	98	96	96	98	99	98	97	96	94	93	96																			
2	111	107	104	102	109	106	103	101	103	100	98	100	98	96	97	96	94	93	91	94	93	91	94	93	91	90	93																			
3	107	103	99	96	106	101	98	95	99	96	94	97	94	92	94	93	91	90	88	92	90	88	87	85	84	87	84																			
4	104	98	94	91	102	97	94	91	95	92	90	94	91	89	92	90	88	87	85	89	87	85	84	82	81	87	81																			
5	101	95	90	87	99	94	90	87	92	89	86	91	88	86	89	87	85	84	82	89	87	85	84	82	81	87	81																			
6	98	91	87	84	96	91	87	84	89	86	83	88	85	83	87	84	82	81	79	87	84	82	81	79	77	87	81																			
7	95	88	84	81	94	87	83	81	86	83	80	85	82	80	84	82	79	78	76	84	82	79	77	76	74	84	78																			
8	92	85	81	78	91	85	81	78	84	80	78	83	80	77	82	79	77	76	74	82	79	77	76	74	72	82	76																			
9	89	82	78	75	88	82	78	75	81	78	75	80	77	75	80	77	75	74	72	80	77	75	74	72	70	80	74																			
10	87	80	76	73	86	80	76	73	79	75	73	78	75	73	78	75	72	71	69	78	75	72	71	69	67	78	71																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	761814
5°	664372
10°	450225
15°	310774
20°	217474
25°	125469
30°	9274
35°	763
40°	408
45°	256
50°	205
55°	229
60°	263
65°	208
70°	256
75°	169
80°	253
85°	0



TEST NUMBER: P179553

CATALOG NUMBER: LDA6A45930D010TE LARH20SP 6LA1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1025.8	29.8
10°-20°	1542.9	44.8
20°-30°	852.1	24.7
30°-40°	16.8	0.5
40°-50°	2.8	0.1
50°-60°	2.2	0.1
60°-70°	1.9	0.1
70°-80°	1.2	0.0
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3420.8	99.3
0°-40°	3437.6	99.8
0°-60°	3442.6	99.9
0°-90°	3445.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3445.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	13897	
5°	12073	###
15°	5476	1543
25°	2074	852
35°	11	17
45°	3	3
55°	2	2
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P179553

CATALOG NUMBER: LDA6A45930D010TE LARH20SP 6LA1LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	13896.6
2.5°	13511.7
5°	12073.0
7.5°	10222.5
10°	8088.0
12.5°	6609.4
15°	5475.8
17.5°	4633.6
20°	3727.8
22.5°	2930.4
25°	2074.3
27.5°	866.7
30°	146.5
32.5°	19.5
35°	11.4
37.5°	7.3
40°	5.7
42.5°	4.1
45°	3.3
47.5°	3.3
50°	2.4
52.5°	2.4
55°	2.4
57.5°	2.4
60°	2.4
62.5°	2.4
65°	1.6
67.5°	1.6
70°	1.6
72.5°	1.6
75°	0.8
77.5°	0.8
80°	0.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)