

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P202731

Luminaire Tested: **LSR6B20D010BZ EC6B10209727 6LBWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P202731
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B20D010BZ EC6B10209727 6LBWH1
Description: PORTFOLIO 6IN CYLINDER
WIDE DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1287.5 lumens
Efficiency: N/A
Efficacy: 61.9 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.16
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P202731

CATALOG NUMBER: LSR6B20D010BZ EC6B10209727 6LBWH1

Luminous Intensity Polar Plot





TEST NUMBER: P202731

CATALOG NUMBER: LSR6B20D010BZ EC6B10209727 6LBWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	101	103	100	98	99	97	95	95	94	93	91																			
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81																			
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	78	75	73																			
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65																			
5	86	75	68	63	84	74	68	63	72	66	62	71	65	61	69	64	61	59																			
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53																			
7	75	64	56	51	73	63	56	51	62	55	51	60	55	51	59	54	50	49																			
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44																			
9	66	55	48	43	65	54	47	43	53	47	43	52	47	42	51	46	42	41																			
10	62	51	44	40	61	50	44	39	50	43	39	49	43	39	48	43	39	38																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P202731

CATALOG NUMBER: LSR6B20D010BZ EC6B10209727 6LBWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	75.0	5.8
10°-20°	212.8	16.5
20°-30°	312.0	24.2
30°-40°	324.7	25.2
40°-50°	224.7	17.5
50°-60°	97.8	7.6
60°-70°	30.0	2.3
70°-80°	9.0	0.7
80°-90°	1.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	599.9	46.6
0°-40°	924.6	71.8
0°-60°	1247.1	96.9
0°-90°	1287.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1287.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	794	
5°	791	75
15°	756	213
25°	682	312
35°	526	325
45°	290	225
55°	105	98
65°	28	30
75°	8	9
85°	2	1
90°	0	



TEST NUMBER: P202731

CATALOG NUMBER: LSR6B20D010BZ EC6B10209727 6LBWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	794.1
2.5°	795.8
5°	790.8
7.5°	784.1
10°	775.8
12.5°	767.4
15°	755.7
17.5°	740.7
20°	724.0
22.5°	705.7
25°	682.3
27.5°	652.3
30°	613.9
32.5°	573.9
35°	525.5
37.5°	472.1
40°	410.4
42.5°	348.7
45°	290.3
47.5°	235.2
50°	186.8
52.5°	141.8
55°	105.1
57.5°	75.1
60°	51.7
62.5°	38.4
65°	28.4
67.5°	21.7
70°	15.0
72.5°	11.7
75°	8.3
77.5°	5.0
80°	3.3
82.5°	1.7
85°	1.7
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)