

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203442

Luminaire Tested: **LSR6B20D010BZ EC6B10208030 6LBMB1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203442
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B20D010BZ EC6B10208030 6LBMB1
Description: PORTFOLIO 6IN CYLINDER
MEDIUM DISTRIBUTION WITH SPECULAR BLACK TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 887.3 lumens
Efficiency: N/A
Efficacy: 42.7 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.86
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203442

CATALOG NUMBER: LSR6B20D010BZ EC6B10208030 6LBMB1

Luminous Intensity Polar Plot





TEST NUMBER: P203442

CATALOG NUMBER: LSR6B20D010BZ EC6B10208030 6LBMB1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																					
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94																																				
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88																																				
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	86	83	82																																				
4	98	91	85	81	96	90	85	81	87	83	80	85	82	79	84	81	78	76																																				
5	93	85	79	75	92	84	79	75	82	78	74	81	77	74	79	76	73	72																																				
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67																																				
7	84	75	69	65	83	75	69	65	73	68	65	72	68	65	71	67	64	63																																				
8	80	71	65	61	79	71	65	61	69	64	61	68	64	61	67	63	60	59																																				
9	77	67	61	58	76	67	61	57	66	61	57	65	60	57	64	60	57	56																																				
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52																																				

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203442

CATALOG NUMBER: LSR6B20D010BZ EC6B10208030 6LBMB1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	101.3	11.4
10°-20°	250.1	28.2
20°-30°	301.2	33.9
30°-40°	190.6	21.5
40°-50°	43.6	4.9
50°-60°	0.5	0.1
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	652.7	73.6
0°-40°	843.2	95.0
0°-60°	887.3	100.0
0°-90°	887.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	887.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1117	
5°	1092	101
15°	892	250
25°	668	301
35°	300	191
45°	48	44
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P203442

CATALOG NUMBER: LSR6B20D010BZ EC6B10208030 6LBMB1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1117.0
2.5°	1112.5
5°	1091.8
7.5°	1052.8
10°	1004.6
12.5°	947.3
15°	892.3
17.5°	839.5
20°	784.5
22.5°	729.4
25°	667.5
27.5°	594.1
30°	504.6
32.5°	403.7
35°	300.5
37.5°	213.3
40°	144.5
42.5°	89.5
45°	48.2
47.5°	20.6
50°	4.6
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)