

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P179569

Luminaire Tested: **LDA6A45930D010TE LARH40FL 6LA1LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P179569
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P26661)
Test Lab: INNOVATION CENTER-P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA6A45930D010TE LARH40FL 6LA1LI
Description: PORTFOLIO 6" Adjustable Reflector, Angle-cut Trim, Self-flanged, 40° Flood
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4085.4 lumens
Efficiency: N/A
Efficacy: 77.1 lumens/watt
Spacing Criteria (0/90/45): 0.66 / 0.66 / 0.61
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct


Input Watts (W): 53
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P179569

CATALOG NUMBER: LDA6A45930D010TE LARH40FL 6LA1LI

Luminous Intensity Polar Plot





TEST NUMBER: P179569

CATALOG NUMBER: LDA6A45930D010TE LARH40FL 6LA1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																	
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	115	112	110	109	112	110	108	107	106	105	104	103	101	100	99	98	98	96																											
2	110	107	103	101	108	105	102	100	102	99	97	99	97	95	96	95	93	92																											
3	107	101	98	94	105	100	97	94	98	95	92	95	93	91	93	91	89	88																											
4	103	97	93	89	101	96	92	89	94	90	88	92	89	87	90	88	86	85																											
5	99	93	88	85	98	92	88	84	90	87	84	89	86	83	87	85	82	81																											
6	96	89	84	81	94	88	84	81	87	83	80	85	82	80	84	81	79	78																											
7	92	85	81	77	91	85	80	77	84	80	77	82	79	76	81	78	76	75																											
8	89	82	77	74	88	82	77	74	81	77	74	80	76	74	79	76	73	72																											
9	86	79	74	71	86	79	74	71	78	74	71	77	73	71	76	73	71	70																											
10	84	76	72	69	83	76	71	69	75	71	68	74	71	68	74	70	68	67																											

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	582442
5°	506971
10°	455848
15°	416773
20°	304497
25°	151067
30°	33379
35°	6478
40°	1166
45°	318
50°	136
55°	76
60°	88
65°	104
70°	128
75°	169
80°	0
85°	0



TEST NUMBER: P179569

CATALOG NUMBER: LDA6A45930D010TE LARH40FL 6LA1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	852.2	20.9
10°-20°	1973.2	48.3
20°-30°	1154.3	28.3
30°-40°	99.1	2.4
40°-50°	4.6	0.1
50°-60°	0.8	0.0
60°-70°	0.8	0.0
70°-80°	0.5	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3979.7	97.4
0°-40°	4078.7	99.8
0°-60°	4084.1	100.0
0°-90°	4085.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4085.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10625	
5°	9213	852
15°	7344	1973
25°	2498	1154
35°	97	99
45°	4	5
55°	1	1
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P179569

CATALOG NUMBER: LDA6A45930D010TE LARH40FL 6LA1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	10624.6
2.5°	9989.8
5°	9212.7
7.5°	8670.7
10°	8189.0
12.5°	7796.7
15°	7343.5
17.5°	6562.2
20°	5219.5
22.5°	3775.9
25°	2497.5
27.5°	1382.6
30°	527.3
32.5°	270.2
35°	96.8
37.5°	30.9
40°	16.3
42.5°	9.0
45°	4.1
47.5°	2.4
50°	1.6
52.5°	0.8
55°	0.8
57.5°	0.8
60°	0.8
62.5°	0.8
65°	0.8
67.5°	0.8
70°	0.8
72.5°	0.8
75°	0.8
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)