

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203339

Luminaire Tested: **LSR6B20D010BZ EC6B10208030 6LBMWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203339
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B20D010BZ EC6B10208030 6LBMWH1
Description: PORTFOLIO 6IN CYLINDER
MEDIUM DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1608.8 lumens
Efficiency: N/A
Efficacy: 77.3 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.85
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203339

CATALOG NUMBER: LSR6B20D010BZ EC6B10208030 6LBMWH1

Luminous Intensity Polar Plot





TEST NUMBER: P203339

CATALOG NUMBER: LSR6B20D010BZ EC6B10208030 6LBMWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																					
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																			
	1	114	111	108	106	111	109	106	104	105	103	101	101	100	98	97	96	95	94																																			
	2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	93	91	89	87																																			
	3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81																																			
	4	97	90	85	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76																																			
	5	93	84	79	74	91	83	78	74	82	77	73	80	76	73	78	75	72	71																																			
	6	88	79	73	69	87	78	73	69	77	72	68	76	71	68	74	70	67	66																																			
	7	84	75	69	64	82	74	68	64	73	68	64	71	67	64	70	66	63	62																																			
	8	80	70	64	60	78	70	64	60	69	64	60	68	63	60	67	62	59	58																																			
	9	76	66	61	57	75	66	60	57	65	60	56	64	59	56	63	59	56	55																																			
	10	72	63	57	53	71	62	57	53	62	57	53	61	56	53	60	56	53	52																																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203339

CATALOG NUMBER: LSR6B20D010BZ EC6B10208030 6LBMWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.5	11.4
10°-20°	450.4	28.0
20°-30°	521.2	32.4
30°-40°	333.1	20.7
40°-50°	94.4	5.9
50°-60°	16.9	1.0
60°-70°	6.9	0.4
70°-80°	2.3	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1155.1	71.8
0°-40°	1488.2	92.5
0°-60°	1599.6	99.4
0°-90°	1608.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1608.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2007	
5°	1971	183
15°	1616	450
25°	1150	521
35°	526	333
45°	110	94
55°	16	17
65°	7	7
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P203339

CATALOG NUMBER: LSR6B20D010BZ EC6B10208030 6LBMWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	2007.0
2.5°	2004.8
5°	1971.2
7.5°	1910.8
10°	1825.8
12.5°	1727.3
15°	1615.5
17.5°	1499.1
20°	1385.0
22.5°	1273.1
25°	1150.1
27.5°	1015.8
30°	865.9
32.5°	698.1
35°	525.8
37.5°	380.4
40°	264.0
42.5°	174.5
45°	109.6
47.5°	64.9
50°	38.0
52.5°	22.4
55°	15.7
57.5°	13.4
60°	11.2
62.5°	8.9
65°	6.7
67.5°	4.5
70°	4.5
72.5°	2.2
75°	2.2
77.5°	2.2
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)