

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P202824

Luminaire Tested: **LSR6B20D010BZ EC6B10208030 6LBWWH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P202824
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B20D010BZ EC6B10208030 6LBWWH1
Description: PORTFOLIO 6IN CYLINDER
WIDE DISTRIBUTION WITH WHEAT TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1863.3 lumens
Efficiency: N/A
Efficacy: 89.6 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.18
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P202824

CATALOG NUMBER: LSR6B20D010BZ EC6B10208030 6LBWWH1

Luminous Intensity Polar Plot





TEST NUMBER: P202824

CATALOG NUMBER: LSR6B20D010BZ EC6B10208030 6LBWWH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20		
RC	80				70				50				30				10		
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30
RCR																			
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	93	92	
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83	
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75	
4	93	84	78	73	91	83	77	72	81	76	71	79	74	71	77	73	70	68	
5	87	77	71	66	85	76	70	65	75	69	65	73	68	64	71	67	63	62	
6	82	71	64	59	80	71	64	59	69	63	59	67	62	58	66	61	58	56	
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51	
8	72	61	54	49	71	61	54	49	59	53	49	58	53	49	57	52	49	47	
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	48	45	43	
10	64	53	46	42	63	53	46	42	52	46	42	51	45	42	50	45	41	40	

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P202824

CATALOG NUMBER: LSR6B20D010BZ EC6B10208030 6LBWWH1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	111.2	6.0
10°-20°	330.8	17.8
20°-30°	498.0	26.7
30°-40°	509.1	27.3
40°-50°	309.2	16.6
50°-60°	87.1	4.7
60°-70°	13.3	0.7
70°-80°	4.3	0.2
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	940.0	50.4
0°-40°	1449.2	77.8
0°-60°	1845.5	99.0
0°-90°	1863.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1863.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1157	
5°	1162	111
15°	1171	331
25°	1087	498
35°	825	509
45°	398	309
55°	86	87
65°	12	13
75°	5	4
85°	0	0
90°	0	



TEST NUMBER: P202824

CATALOG NUMBER: LSR6B20D010BZ EC6B10208030 6LBWWH1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1157.3
2.5°	1157.3
5°	1162.0
7.5°	1169.0
10°	1169.0
12.5°	1173.7
15°	1171.4
17.5°	1166.7
20°	1150.3
22.5°	1126.9
25°	1087.2
27.5°	1042.8
30°	982.0
32.5°	909.5
35°	825.3
37.5°	731.8
40°	624.3
42.5°	512.0
45°	397.5
47.5°	294.6
50°	208.1
52.5°	140.3
55°	86.5
57.5°	51.4
60°	25.7
62.5°	16.4
65°	11.7
67.5°	9.4
70°	7.0
72.5°	4.7
75°	4.7
77.5°	2.3
80°	2.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)