

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204686

Luminaire Tested: **LSR6B20D010BZ EC6B10209030 6LBPSMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204686
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B20D010BZ EC6B10209030 6LBPSMW1
Description: PORTFOLIO 6IN CYLINDER
SHALLOW DISTRIBUTION WITH PLASTIC MATTE WHITE TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1953.7 lumens
Efficiency: N/A
Efficacy: 93.9 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204686

CATALOG NUMBER: LSR6B20D010BZ EC6B10209030 6LBPSMW1

Luminous Intensity Polar Plot






TEST NUMBER: P204686

CATALOG NUMBER: LSR6B20D010BZ EC6B10209030 6LBPSMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86																			
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74																			
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63																			
4	85	74	66	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54																			
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47																			
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42																			
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37																			
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33																			
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30																			
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27																			

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204686

CATALOG NUMBER: LSR6B20D010BZ EC6B10209030 6LBPSMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.6	3.8
10°-20°	212.6	10.9
20°-30°	320.2	16.4
30°-40°	381.0	19.5
40°-50°	380.3	19.5
50°-60°	309.3	15.8
60°-70°	190.3	9.7
70°-80°	73.7	3.8
80°-90°	11.8	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	607.4	31.1
0°-40°	988.4	50.6
0°-60°	1677.9	85.9
0°-90°	1953.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1953.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	787	
5°	785	75
15°	755	213
25°	697	320
35°	610	381
45°	494	380
55°	346	309
65°	191	190
75°	67	74
85°	9	12
90°	0	



TEST NUMBER: P204686

CATALOG NUMBER: LSR6B20D010BZ EC6B10209030 6LBPSMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	787.2
2.5°	788.3
5°	784.9
7.5°	780.2
10°	774.4
12.5°	764.0
15°	754.8
17.5°	740.9
20°	725.8
22.5°	711.9
25°	696.9
27.5°	676.0
30°	655.2
32.5°	635.5
35°	610.1
37.5°	582.3
40°	556.8
42.5°	525.6
45°	494.3
47.5°	460.7
50°	424.8
52.5°	387.8
55°	346.1
57.5°	305.6
60°	266.2
62.5°	228.0
65°	191.0
67.5°	156.3
70°	123.9
72.5°	93.8
75°	67.1
77.5°	44.0
80°	26.6
82.5°	16.2
85°	9.3
87.5°	4.6
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)