

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204483

Luminaire Tested: **LSR6B20D010BZ EC6B10209730 6LBSB1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P204483  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR6B20D010BZ EC6B10209730 6LBSB1  
Description: PORTFOLIO 6IN CYLINDER  
SHALLOW DISTRIBUTION WITH SPECULAR BLACK TRIM  
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W  
DL3-21.8 6 W DLE-22.46 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1392.6 lumens  
Efficiency: N/A  
Efficacy: 67.0 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.3  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 20.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P204483

CATALOG NUMBER: LSR6B20D010BZ EC6B10209730 6LBSB1

### Luminous Intensity Polar Plot





TEST NUMBER: P204483

CATALOG NUMBER: LSR6B20D010BZ EC6B10209730 6LBSB1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	103	100	108	105	101	98	100	98	95	97	94	93	93	91	90	88			
2	102	95	89	84	100	93	88	83	90	85	81	86	83	79	84	80	78	76			
3	94	84	77	72	91	83	76	71	80	74	70	77	73	68	75	71	67	65			
4	86	76	68	62	84	74	67	61	72	65	60	70	64	60	68	63	59	57			
5	80	68	60	54	78	67	59	53	65	58	53	63	57	52	61	56	52	50			
6	74	62	53	47	72	61	53	47	59	52	47	57	51	46	56	50	46	44			
7	69	56	48	42	67	55	48	42	54	47	42	52	46	41	51	45	41	39			
8	64	51	43	38	63	51	43	38	49	42	37	48	42	37	47	41	37	35			
9	60	47	39	34	59	47	39	34	46	39	34	45	38	34	44	38	34	32			
10	56	44	36	31	55	43	36	31	42	36	31	41	35	31	40	35	31	29			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P204483

CATALOG NUMBER: LSR6B20D010BZ EC6B10209730 6LBSB1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	58.0	4.2
10°-20°	164.5	11.8
20°-30°	244.7	17.6
30°-40°	284.8	20.4
40°-50°	277.6	19.9
50°-60°	213.5	15.3
60°-70°	118.0	8.5
70°-80°	31.3	2.2
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	467.2	33.6
0°-40°	752.0	54.0
0°-60°	1243.1	89.3
0°-90°	1392.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1392.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	614	
5°	611	58
15°	583	165
25°	531	245
35°	457	285
45°	360	278
55°	238	213
65°	118	118
75°	26	31
85°	0	0
90°	0	



TEST NUMBER: P204483

CATALOG NUMBER: LSR6B20D010BZ EC6B10209730 6LBSB1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	614.3
2.5°	614.3
5°	610.8
7.5°	605.5
10°	602.0
12.5°	591.4
15°	582.6
17.5°	573.7
20°	561.4
22.5°	549.0
25°	531.4
27.5°	513.7
30°	496.1
32.5°	476.6
35°	457.2
37.5°	432.5
40°	411.3
42.5°	388.4
45°	360.1
47.5°	333.7
50°	303.6
52.5°	271.9
55°	238.3
57.5°	206.5
60°	176.5
62.5°	146.5
65°	118.3
67.5°	91.8
70°	67.1
72.5°	45.9
75°	26.5
77.5°	12.4
80°	1.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)