

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203215

Luminaire Tested: **LSR6B10D010BZ EC6B10209024 6LBMH1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203215
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B10D010BZ EC6B10209024 6LBMH1
Description: PORTFOLIO 6IN CYLINDER
MEDIUM DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W
DL3-11.1 W DLE-11.39 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 561.2 lumens
Efficiency: N/A
Efficacy: 56.7 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.93
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203215

CATALOG NUMBER: LSR6B10D010BZ EC6B10209024 6LBMH1

Luminous Intensity Polar Plot





TEST NUMBER: P203215

CATALOG NUMBER: LSR6B10D010BZ EC6B10209024 6LBMH1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|--|--|--|--|--|--|----|--|--|--|--|--|--|--|--|---|
| RF | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | |
| RC | 80 | | | | | | | | | 50 | | | | | | | | | 30 | | | | | | | | | 10 | | | | | | | | | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 | | | | | | | | | | | | | | | | |
| RCR | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | | | | | | | | | | | | | | | | | |
| 1 | 113 | 110 | 107 | 105 | 111 | 108 | 105 | 103 | 104 | 102 | 100 | 100 | 99 | 97 | 97 | 95 | 94 | 92 | | | | | | | | | | | | | | | | | | | |
| 2 | 107 | 102 | 97 | 93 | 105 | 100 | 96 | 92 | 97 | 93 | 90 | 94 | 91 | 88 | 91 | 89 | 87 | 85 | | | | | | | | | | | | | | | | | | | |
| 3 | 101 | 94 | 88 | 84 | 99 | 92 | 88 | 84 | 90 | 86 | 82 | 87 | 84 | 81 | 85 | 82 | 80 | 78 | | | | | | | | | | | | | | | | | | | |
| 4 | 95 | 87 | 81 | 76 | 93 | 86 | 80 | 76 | 84 | 79 | 75 | 82 | 78 | 74 | 80 | 76 | 73 | 72 | | | | | | | | | | | | | | | | | | | |
| 5 | 90 | 81 | 75 | 70 | 88 | 80 | 74 | 70 | 78 | 73 | 69 | 76 | 72 | 68 | 75 | 71 | 68 | 66 | | | | | | | | | | | | | | | | | | | |
| 6 | 85 | 75 | 69 | 64 | 83 | 75 | 69 | 64 | 73 | 68 | 64 | 72 | 67 | 63 | 70 | 66 | 63 | 61 | | | | | | | | | | | | | | | | | | | |
| 7 | 80 | 70 | 64 | 59 | 79 | 70 | 64 | 59 | 68 | 63 | 59 | 67 | 62 | 59 | 66 | 62 | 58 | 57 | | | | | | | | | | | | | | | | | | | |
| 8 | 76 | 66 | 60 | 55 | 75 | 65 | 59 | 55 | 64 | 59 | 55 | 63 | 58 | 55 | 62 | 58 | 54 | 53 | | | | | | | | | | | | | | | | | | | |
| 9 | 72 | 62 | 56 | 51 | 71 | 61 | 55 | 51 | 60 | 55 | 51 | 60 | 55 | 51 | 59 | 54 | 51 | 49 | | | | | | | | | | | | | | | | | | | |
| 10 | 69 | 58 | 52 | 48 | 68 | 58 | 52 | 48 | 57 | 52 | 48 | 56 | 51 | 48 | 55 | 51 | 48 | 46 | | | | | | | | | | | | | | | | | | | |

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203215

CATALOG NUMBER: LSR6B10D010BZ EC6B10209024 6LBMH1

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 50.8 | 9.0 |
| 10°-20° | 131.4 | 23.4 |
| 20°-30° | 170.2 | 30.3 |
| 30°-40° | 126.4 | 22.5 |
| 40°-50° | 53.4 | 9.5 |
| 50°-60° | 18.9 | 3.4 |
| 60°-70° | 7.3 | 1.3 |
| 70°-80° | 2.5 | 0.5 |
| 80°-90° | 0.3 | 0.1 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 352.4 | 62.8 |
| 0°-40° | 478.8 | 85.3 |
| 0°-60° | 551.1 | 98.2 |
| 0°-90° | 561.2 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 561.2 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|-----|------|
| 0° | 555 | |
| 5° | 543 | 51 |
| 15° | 469 | 131 |
| 25° | 378 | 170 |
| 35° | 200 | 126 |
| 45° | 66 | 53 |
| 55° | 20 | 19 |
| 65° | 7 | 7 |
| 75° | 2 | 3 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P203215

CATALOG NUMBER: LSR6B10D010BZ EC6B10209024 6LBMH1

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|-------|
| 0° | 555.4 |
| 2.5° | 553.8 |
| 5° | 543.4 |
| 7.5° | 528.2 |
| 10° | 509.7 |
| 12.5° | 489.7 |
| 15° | 468.8 |
| 17.5° | 445.6 |
| 20° | 424.8 |
| 22.5° | 403.1 |
| 25° | 377.5 |
| 27.5° | 342.2 |
| 30° | 300.5 |
| 32.5° | 251.7 |
| 35° | 200.4 |
| 37.5° | 157.1 |
| 40° | 119.4 |
| 42.5° | 89.0 |
| 45° | 65.7 |
| 47.5° | 48.1 |
| 50° | 35.3 |
| 52.5° | 26.4 |
| 55° | 20.0 |
| 57.5° | 15.2 |
| 60° | 12.0 |
| 62.5° | 8.8 |
| 65° | 7.2 |
| 67.5° | 5.6 |
| 70° | 4.0 |
| 72.5° | 3.2 |
| 75° | 2.4 |
| 77.5° | 1.6 |
| 80° | 0.8 |
| 82.5° | 0.8 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)