

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204887

Luminaire Tested: **LSR6B20D010BZ EC6B10208035 6LBCSMB1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P204887  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR6B20D010BZ EC6B10208035 6LBCSMB1  
Description: PORTFOLIO 6IN CYLINDER  
SHALLOW DISTRIBUTION WITH CAST MATTE BLACK TRIM  
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W  
DL3-21.8 6 W DLE-22.46 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1938.3 lumens  
Efficiency: N/A  
Efficacy: 93.2 lumens/watt  
Spacing Criteria (0/90/45): 1.23 / 1.23 / 1.33  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 20.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P204887

CATALOG NUMBER: LSR6B20D010BZ EC6B10208035 6LBCSMB1

### Luminous Intensity Polar Plot





TEST NUMBER: P204887

CATALOG NUMBER: LSR6B20D010BZ EC6B10208035 6LBCSMB1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	103	100	108	104	101	98	100	98	95	96	94	92	93	91	90	88			88
2	102	95	89	84	99	93	87	83	89	85	81	86	82	79	83	80	77	75			75
3	93	84	77	71	91	83	76	70	80	74	69	77	72	68	74	70	67	65			65
4	86	75	67	61	84	74	66	61	71	65	60	69	63	59	67	62	58	56			56
5	79	67	59	53	77	66	59	53	64	57	52	62	56	52	61	55	51	49			49
6	74	61	53	47	72	60	52	46	58	51	46	57	50	46	55	50	45	43			43
7	68	55	47	41	67	55	47	41	53	46	41	52	45	41	50	45	40	39			39
8	64	51	43	37	62	50	42	37	49	42	37	48	41	37	46	41	36	35			35
9	60	47	39	33	58	46	39	33	45	38	33	44	38	33	43	37	33	31			31
10	56	43	35	30	55	43	35	30	42	35	30	41	34	30	40	34	30	28			28

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P204887

CATALOG NUMBER: LSR6B20D010BZ EC6B10208035 6LBCSMB1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	77.4	4.0
10°-20°	220.5	11.4
20°-30°	331.5	17.1
30°-40°	393.4	20.3
40°-50°	389.3	20.1
50°-60°	305.8	15.8
60°-70°	171.4	8.8
70°-80°	48.1	2.5
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	629.5	32.5
0°-40°	1022.9	52.8
0°-60°	1718.0	88.6
0°-90°	1938.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1938.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	818	
5°	817	77
15°	782	221
25°	720	332
35°	631	393
45°	507	389
55°	345	306
65°	171	171
75°	42	48
85°	0	1
90°	0	



TEST NUMBER: P204887

CATALOG NUMBER: LSR6B20D010BZ EC6B10208035 6LBCSMB1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	818.4
2.5°	815.7
5°	817.1
7.5°	810.1
10°	801.8
12.5°	792.0
15°	782.3
17.5°	769.8
20°	753.1
22.5°	736.5
25°	719.8
27.5°	701.7
30°	678.1
32.5°	654.5
35°	630.9
37.5°	603.1
40°	571.1
42.5°	540.5
45°	507.2
47.5°	469.7
50°	430.8
52.5°	386.3
55°	344.6
57.5°	297.4
60°	252.9
62.5°	212.6
65°	170.9
67.5°	134.8
70°	100.0
72.5°	68.1
75°	41.7
77.5°	20.8
80°	5.6
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)