

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P205091

Luminaire Tested: **LSR6B20D010BZ EC6B10208035 6LBMLI1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P205091  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR6B20D010BZ EC6B10208035 6LBMLI1  
Description: PORTFOLIO 6IN CYLINDER  
MEDIUM DISTRIBUTION WITH SPECULAR CLEAR TRIM  
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W  
DL3-21.8 6 W DLE-22.46 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1868.9 lumens  
Efficiency: N/A  
Efficacy: 89.8 lumens/watt  
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.85  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 20.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P205091

CATALOG NUMBER: LSR6B20D010BZ EC6B10208035 6LBMLI1

### Luminous Intensity Polar Plot





TEST NUMBER: P205091

CATALOG NUMBER: LSR6B20D010BZ EC6B10208035 6LBML11

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94						94													
2	108	103	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88						88													
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	85	83	82						82													
4	98	91	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76						76													
5	93	85	79	75	91	84	79	75	82	78	74	81	77	73	79	76	73	71						71													
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67						67													
7	84	75	69	65	83	75	69	65	73	68	65	72	68	64	71	67	64	63						63													
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59						59													
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55						55													
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52						52													

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P205091

CATALOG NUMBER: LSR6B20D010BZ EC6B10208035 6LBML11

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	215.4	11.5
10°-20°	536.4	28.7
20°-30°	623.5	33.4
30°-40°	381.8	20.4
40°-50°	94.8	5.1
50°-60°	11.1	0.6
60°-70°	4.1	0.2
70°-80°	1.6	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1375.4	73.6
0°-40°	1757.2	94.0
0°-60°	1863.1	99.7
0°-90°	1868.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1868.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2339	
5°	2308	215
15°	1925	536
25°	1380	624
35°	598	382
45°	105	95
55°	10	11
65°	5	4
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P205091

CATALOG NUMBER: LSR6B20D010BZ EC6B10208035 6LBML11

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2338.7
2.5°	2336.3
5°	2307.6
7.5°	2245.5
10°	2161.8
12.5°	2051.8
15°	1925.0
17.5°	1788.7
20°	1654.8
22.5°	1520.9
25°	1379.8
27.5°	1217.2
30°	1030.7
32.5°	813.1
35°	597.8
37.5°	420.9
40°	287.0
42.5°	179.4
45°	105.2
47.5°	59.8
50°	31.1
52.5°	14.3
55°	9.6
57.5°	7.2
60°	7.2
62.5°	4.8
65°	4.8
67.5°	2.4
70°	2.4
72.5°	2.4
75°	2.4
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)