

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204034

Luminaire Tested: **LSR6B10D010BZ EC6B10208027 6LBNMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P204034
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B10D010BZ EC6B10208027 6LBNMW1
Description: PORTFOLIO 6IN CYLINDER
NARROW DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-10.05 W DE010-10.58 W D5LT-10.2 W DMX-10.6 W DL2-11.8 W
DL3-11.1 W DLE-11.39 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 734.0 lumens
Efficiency: N/A
Efficacy: 74.1 lumens/watt
Spacing Criteria (0/90/45): 0.99 / 0.99 / 0.97
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 9.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P204034

CATALOG NUMBER: LSR6B10D010BZ EC6B10208027 6LBNMW1

Luminous Intensity Polar Plot





TEST NUMBER: P204034

CATALOG NUMBER: LSR6B10D010BZ EC6B10208027 6LBNMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	108	105	103	109	106	103	101	102	100	98	98	97	95	95	93	92	90		
2	105	99	94	90	102	97	92	89	94	90	87	91	87	85	88	85	83	81		
3	98	90	84	79	96	89	83	79	86	81	77	84	80	76	81	78	75	73		
4	92	83	76	71	90	82	76	71	80	74	70	77	73	69	75	71	68	66		
5	87	77	70	64	85	76	69	64	74	68	64	72	67	63	70	66	62	61		
6	81	71	64	59	80	70	63	59	68	63	58	67	62	58	66	61	57	56		
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51		
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47		
9	69	58	51	46	67	57	51	46	56	50	46	55	50	46	54	49	46	44		
10	65	54	47	43	64	54	47	43	53	47	43	52	46	43	51	46	43	41		

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P204034

CATALOG NUMBER: LSR6B10D010BZ EC6B10208027 6LBNMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.9	7.6
10°-20°	148.2	20.2
20°-30°	197.8	26.9
30°-40°	159.6	21.7
40°-50°	76.5	10.4
50°-60°	45.4	6.2
60°-70°	30.1	4.1
70°-80°	16.2	2.2
80°-90°	4.4	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	401.8	54.7
0°-40°	561.4	76.5
0°-60°	683.2	93.1
0°-90°	734.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	734.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	602	
5°	595	56
15°	527	148
25°	433	198
35°	256	160
45°	94	76
55°	50	45
65°	30	30
75°	15	16
85°	4	4
90°	0	



TEST NUMBER: P204034

CATALOG NUMBER: LSR6B10D010BZ EC6B10208027 6LBNMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	601.9
2.5°	601.9
5°	594.9
7.5°	583.3
10°	566.9
12.5°	549.4
15°	527.3
17.5°	506.3
20°	482.9
22.5°	458.4
25°	432.8
27.5°	405.9
30°	367.4
32.5°	313.8
35°	255.5
37.5°	201.8
40°	156.3
42.5°	121.3
45°	94.5
47.5°	74.7
50°	63.0
52.5°	56.0
55°	50.2
57.5°	45.5
60°	39.7
62.5°	35.0
65°	30.3
67.5°	25.7
70°	22.2
72.5°	18.7
75°	15.2
77.5°	11.7
80°	9.3
82.5°	7.0
85°	3.5
87.5°	1.2
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)