

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P204577

Luminaire Tested: **LSR6B20D010BZ EC6B10208035 6LBSMW1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P204577  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LSR6B20D010BZ EC6B10208035 6LBSMW1  
Description: PORTFOLIO 6IN CYLINDER  
SHALLOW DISTRIBUTION WITH MATTE WHITE TRIM  
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W  
DL3-21.8 6 W DLE-22.46 W  
Light Source: HIGH LUMEN LED  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2344.0 lumens  
Efficiency: N/A  
Efficacy: 112.7 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.34  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 20.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P204577

CATALOG NUMBER: LSR6B20D010BZ EC6B10208035 6LBSMW1

### Luminous Intensity Polar Plot





TEST NUMBER: P204577

CATALOG NUMBER: LSR6B20D010BZ EC6B10208035 6LBSMW1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	88	86																			
2	101	93	87	82	98	92	86	81	88	83	79	85	81	77	82	79	76	74																			
3	93	83	75	69	90	81	74	69	78	72	67	76	70	66	73	69	65	63																			
4	85	74	65	59	83	72	65	59	70	63	58	68	62	57	66	61	56	54																			
5	78	66	58	51	76	65	57	51	63	56	51	61	55	50	59	54	49	47																			
6	73	60	51	45	71	59	51	45	57	50	44	55	49	44	54	48	44	42																			
7	67	54	46	40	66	54	46	40	52	45	40	51	44	39	49	43	39	37																			
8	63	50	41	36	61	49	41	36	48	41	35	46	40	35	45	39	35	33																			
9	59	46	38	32	57	45	37	32	44	37	32	43	36	32	42	36	32	30																			
10	55	42	34	29	54	42	34	29	41	34	29	40	33	29	39	33	29	27																			

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P204577

CATALOG NUMBER: LSR6B20D010BZ EC6B10208035 6LBSMW1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	89.5	3.8
10°-20°	255.1	10.9
20°-30°	384.2	16.4
30°-40°	457.1	19.5
40°-50°	456.2	19.5
50°-60°	371.1	15.8
60°-70°	228.3	9.7
70°-80°	88.4	3.8
80°-90°	14.2	0.6
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	728.7	31.1
0°-40°	1185.8	50.6
0°-60°	2013.1	85.9
0°-90°	2344.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2344.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	944	
5°	942	89
15°	906	255
25°	836	384
35°	732	457
45°	593	456
55°	415	371
65°	229	228
75°	81	88
85°	11	14
90°	0	



TEST NUMBER: P204577

CATALOG NUMBER: LSR6B20D010BZ EC6B10208035 6LBSMW1

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	944.4
2.5°	945.8
5°	941.6
7.5°	936.1
10°	929.1
12.5°	916.6
15°	905.5
17.5°	888.8
20°	870.8
22.5°	854.1
25°	836.1
27.5°	811.1
30°	786.1
32.5°	762.5
35°	731.9
37.5°	698.6
40°	668.0
42.5°	630.5
45°	593.0
47.5°	552.7
50°	509.7
52.5°	465.3
55°	415.3
57.5°	366.6
60°	319.4
62.5°	273.6
65°	229.2
67.5°	187.5
70°	148.6
72.5°	112.5
75°	80.6
77.5°	52.8
80°	31.9
82.5°	19.4
85°	11.1
87.5°	5.6
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)