

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P203134

Luminaire Tested: **LSR6B20D010BZ EC6B10208035 6LBWMW1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P203134
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P35319)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LSR6B20D010BZ EC6B10208035 6LBWMW1
Description: PORTFOLIO 6IN CYLINDER
WIDE DISTRIBUTION WITH MATTE WHITE TRIM
WATTAGE D010TR-21.86 W DE010-20.46 W D5LT-21.24 W DMX-20.89 W DL2-22.5 W
DL3-21.8 6 W DLE-22.46 W
Light Source: HIGH LUMEN LED
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1974.1 lumens
Efficiency: N/A
Efficacy: 94.9 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.13 / 1.15
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 20.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P203134

CATALOG NUMBER: LSR6B20D010BZ EC6B10208035 6LBWMW1

Luminous Intensity Polar Plot





TEST NUMBER: P203134

CATALOG NUMBER: LSR6B20D010BZ EC6B10208035 6LBWMW1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	
1	111	107	104	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88	88	
2	103	96	90	86	100	94	89	85	91	86	83	88	84	81	85	82	79	77	77	
3	95	86	80	74	93	85	79	74	82	77	72	80	75	71	77	73	70	68	68	
4	89	78	71	65	86	77	70	65	75	69	64	72	67	63	70	66	62	60	60	
5	82	71	64	58	80	70	63	58	68	62	57	66	61	56	65	60	56	54	54	
6	77	65	57	52	75	64	57	52	63	56	51	61	55	51	60	54	50	49	49	
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44	44	
8	67	55	48	42	66	55	47	42	53	47	42	52	46	42	51	46	42	40	40	
9	63	51	44	39	62	51	44	39	50	43	39	49	43	38	48	42	38	37	37	
10	60	48	40	36	58	47	40	36	46	40	36	45	40	35	45	39	35	34	34	

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P203134

CATALOG NUMBER: LSR6B20D010BZ EC6B10208035 6LBWMW1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	104.4	5.3
10°-20°	292.8	14.8
20°-30°	421.8	21.4
30°-40°	438.0	22.2
40°-50°	323.8	16.4
50°-60°	193.4	9.8
60°-70°	117.5	6.0
70°-80°	64.4	3.3
80°-90°	17.9	0.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	819.0	41.5
0°-40°	1257.0	63.7
0°-60°	1774.2	89.9
0°-90°	1974.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1974.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1109	
5°	1101	104
15°	1039	293
25°	919	422
35°	706	438
45°	417	324
55°	211	193
65°	117	118
75°	60	64
85°	14	18
90°	0	



TEST NUMBER: P203134

CATALOG NUMBER: LSR6B20D010BZ EC6B10208035 6LBWMW1

CANDELA DISTRIBUTION (FULL):

	0°
0°	1108.6
2.5°	1108.6
5°	1101.4
7.5°	1091.8
10°	1077.4
12.5°	1060.7
15°	1039.1
17.5°	1015.2
20°	991.2
22.5°	957.7
25°	919.4
27.5°	878.7
30°	826.0
32.5°	773.4
35°	706.3
37.5°	636.9
40°	560.3
42.5°	486.0
45°	416.6
47.5°	354.4
50°	299.3
52.5°	251.4
55°	210.7
57.5°	179.6
60°	153.2
62.5°	134.1
65°	117.3
67.5°	103.0
70°	88.6
72.5°	74.2
75°	59.9
77.5°	47.9
80°	35.9
82.5°	26.3
85°	14.4
87.5°	7.2
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)